



Perfect sparkle, easy application

MASTERColour CDM-Rm Elite Mini

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Easy to install and replace, reducing installation and relamping costs
- Fits in small luminaires which are less visible

Features

- Crisp white sparkling light
- Excellent colour rendering, with extra red
- High efficacy with unparalleled lumen maintenance
- Mini design fitting in open luminaires
- UV-blocking front glass

Application

- Accent and display lighting in retail
- General and decorative indoor lighting

Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)


MASTERColour CDM-Rm Elite Mini

Versions



LPPR CDM-Rm 0008

Dimensional drawing



Product	D (max)	D	C (max)	C	C1 (max)	A (max)
CDM-Rm Elite Mini 20W/830 GX10 MR16 40D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm
CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm

General Information	
Cap-Base	GX10
Switching Cycle	1,350
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	40 degree(s)
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.398
Correlated Color Temperature (Nom)	3000 K
Operating and Electrical	
Warm-up time to 60% light	120 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16

Light Technical (1/2)

Order Code	Full Product Name	Color rendering index (CRI)	LLMF At End Of Nominal Lifetime (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
928191205331	CDM-Rm Elite Mini 20W/830 GX10 MR16 40D	84	70 %	50 lm/W	860 lm
928194805330	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	90	80 %	61 lm/W	2,150 lm

Light Technical (2/2)

Order Code	Full Product Name	Luminous Intensity (Nom)
928191205331	CDM-Rm Elite Mini 20W/830 GX10 MR16 40D	1,750 cd

MASTERCcolour CDM-Rm Elite Mini

Order Code	Full Product Name	Luminous Intensity (Nom)
928194805330	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	3,600 cd



Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928191205331	CDM-Rm Elite Mini 20W/830	95 V	20.1 W
	GX10 MR16 40D		


Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928194805330	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	87 V	39.1 W

Approval and Application


Order Code	Full Product Name	Energy	Mercury (Hg)	Mercury (Hg)
		Consumption	Content	Content
		kWh/1000 h	(Max)	(Nom)
928191205331	CDM-Rm Elite Mini 20W/830 GX10 MR16 40D	21 kWh	3.5 mg	3.5 mg
928194805330	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	40 kWh	4.7 mg	4.7 mg



Accent Diagrams




**Accent Diagram - CDM-Rm Elite Mini 20W/830
GX10 MR16 40D**




**Accent Diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 40D**

MASTERColour CDM-Rm Elite Mini

Beam Diagrams



Beam diagram - CDM-Rm Elite Mini 20W/830
GX10 MR16 40D



Beam diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 40D

