



Product Description

MASTERColour CDM-R

Range of compact, high-efficiency, discharge reflector lamps with a stable colour over lifetime and a crisp, sparkling light

Benefits

- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Stable colour impression over lifetime
- Unique design increases flexibility in application and allows powerful accents from small, unobtrusive luminaires
- Simplified luminaire design because CDM-R lamps can be used in open luminaires
- Relatively low heat output enhances comfort for shoppers and staff
- Integrated UV-Block shield reduces fading risks

Features

- Warm or cool white colour impression with good colour rendering
- High beam intensities are achieved very easy and efficiently from these compact reflector lamps

Application

- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Colour 830 lamps may also use electromagnetic gear.


MASTERCoulour CDM-R

Versions




LPPR CDM-R 0001


Dimensional drawing



Product	D (max)	D	C (max)	C
MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm




Accent Diagrams



Accent Diagram - MASTERC CDM-R 70W/830
E27 PAR30L 40D 1CT

MASTERColour CDM-R

Beam Diagrams



Beam diagram - MASTERC CDM-R 70W/830
E27 PAR30L 40D 1CT

