



產品說明

MASTERColour CDM-TC 陶瓷複金屬燈

超精巧、高效率單端型放電燈，光色歷久如新，光線清晰明亮

优点

- 使用壽命優於白熾燈與鹵素燈
- 石英外管阻隔紫外線，避免光照導致商品褪色
- 歷久如新的穩定光色
- 高效率燈具，節省運作成本，降低光照熱度 (使顧客與工作人員更感舒適)

特点

- 清晰明亮的白色光
- 絕佳的演色性
- 迷你燈具也能展現高強度光束照明效果

应用

- 重點與展示照明，提供清亮晶瑩的照明效果
- 一般與裝飾照明

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTERColour CDM-TC 陶瓷複金屬燈

Versions



LPPR CDM-TC 0001

二维绘图



| Product | D (max) | D | O | L (min) | L (max) | L | C (max) |
|------------------------|---------|--------|------|---------|---------|-------|---------|
| MASTERC CDM-TC 35W/830 | 15 mm | 0.5 in | 5 mm | 51 mm | 53 mm | 52 mm | 85 mm |
| G8.5 1CT/12 | | | | | | | |

