



Product Description

MASTERColour CDM-T Elite

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp

Benefits

- Outstanding rendering of displayed merchandise due to high colour rendering (Ra 90) in combination with high lumen output; best offer in the market for 'enhancing merchandize'
- Excellent colour quality, which remains stable over lifetime
- Light output over lifetime maintains display brightness
- High efficacy and long lifetime for lowest operating costs and low heat generation
- Relatively low heat generation enhances comfort for shoppers and staff
- UV Block for reduced fading risk of merchandise

Features

- Crisp white light
- Excellent colour rendering (Ra 90)
- Reliable lifetime performance
- Stable colour performance during lifetime
- Increased light output compared with regular MASTERColour lamps
- Improved maintenance compared with regular MASTERColour lamps
- Burning position for
 - CDM Elite-T 35W: vertical +/- 60 degrees
 - CDM Elite-T 70W: universal

Application

- Accent and display lighting with a sparkling effect, excellent solution for Retail
- Decorative outdoor floodlighting

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR_CDM-T-E_150W_930-Product photo



LPPR_CDM-T-E_100W_G12-Product photo



LPPR_CDM-T 0005




LPPR_CDM-T-E_0004-Product photo



LPPR_CDM-T-E_0005-Product photo



Dimensional drawing



Product	D (max)	D O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 20W/830	20 mm	4 mm	55 mm	57 mm	56 mm	103 mm
G12 1CT/12						

MASTERColour CDM-T Elite

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 150W/930 G12 1CT/12	20 mm	9 mm	55 mm	57 mm	56 mm	110 mm

Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 100W/930 G12 1CT/12	20 mm	8.5 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 35W/942 G12 1CT	20 mm	5.2 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 50W/930 G12 1CT/12	20 mm	6 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 50W/942 G12 1CT	20 mm	7.1 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/942 G12 1CT	20 mm	7.75 mm	55 mm	57 mm	56 mm	103 mm

General Information	
Cap base	G12
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T19

General Information

Order Code	Full Product Name	Operating position
21312915	MASTERC CDM-T ELITE 150W/930 G12 1CT/12	P10
87169200	MASTERColour CDM-T Elite 100W/930 G12 1CT/12	UNIVERSAL
87156200	MASTERColour CDM-T Elite 20W/830 G12.1CT/12	UNIVERSAL
91137400	MasterC CDM-T Elite 35W/930 G12 1CT/12	UNIVERSAL
16364000	MASTERColour CDM-T Elite 35W/942 G12 1CT	UNIVERSAL

Order Code	Full Product Name	Operating position
91141100	MASTERColour CDM-T Elite 70W/930 G12 1CT/12	UNIVERSAL
16362600	MASTERColour CDM-T Elite 70W/942 G12 1CT	UNIVERSAL
20159500	MASTERColour CDM-T Elite 50W/942 G12 1CT	UNIVERSAL
93060300	MASTERColour CDM-T Elite 50W/930 G12 1CT/12	UNIVERSAL

Light Technical

MASTERColour CDM-T Elite

Order Code	Full Product Name	Chromaticity	Chromaticity	Colour designation	Correlated Colour	Colour	Luminous efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)		Temperature (Nom)	rendering index (CRI)		
21312915	MASTERC CDM-T ELITE 150W/930 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	92	98 lm/W	14,600 lm
87169200	MASTERColour CDM-T Elite 100W/930 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	92	110 lm/W	11,000 lm
87156200	MASTERColour CDM-T Elite 20W/830 G12.1CT/12	0.434	0.398	Warm White (WW)	3000 K	84	90 lm/W	1,800 lm
91137400	MasterC CDM-T Elite 35W/930 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	90	98 lm/W	4,050 lm
16364000	MASTERColour CDM-T Elite 35W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	90	98 lm/W	3,850 lm
91141100	MASTERColour CDM-T Elite 70W/930 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	90	103 lm/W	7,800 lm
16362600	MASTERColour CDM-T Elite 70W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	90	100 lm/W	7,500 lm
20159500	MASTERColour CDM-T Elite 50W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	90	100 lm/W	5,000 lm
93060300	MASTERColour CDM-T Elite 50W/930 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	90	108 lm/W	5,450 lm

Operating and Electrical

Order Code	Full Product Name	Voltage	Power
		(nom.)	Consumption
21312915	MASTERC CDM-T ELITE 150W/930 G12 1CT/12	92 V	150.1 W
87169200	MASTERColour CDM-T Elite 100W/930 G12 1CT/12	88 V	100.1 W
87156200	MASTERColour CDM-T Elite 20W/830 G12.1CT/12	95 V	20.1 W
91137400	MasterC CDM-T Elite 35W/930 G12 1CT/12	85 V	39.1 W
16364000	MASTERColour CDM-T Elite 35W/942 G12 1CT	90 V	39.1 W

Order Code	Full Product Name	Voltage	Power
		(nom.)	Consumption
91141100	MASTERColour CDM-T Elite 70W/930 G12 1CT/12	85 V	73.2 W
16362600	MASTERColour CDM-T Elite 70W/942 G12 1CT	87 V	73.2 W
20159500	MASTERColour CDM-T Elite 50W/942 G12 1CT	91 V	50.2 W
93060300	MASTERColour CDM-T Elite 50W/930 G12 1CT/12	90 V	50.2 W

Approval and Application

Order Code	Full Product Name	Energy	Mercury	Mercury
		consumption kWh/1,000 hours	(Hg) content (max.)	(Hg) content (nom.)
21312915	MASTERC CDM-T ELITE 150W/930 G12 1CT/12	151 kWh	9.5 mg	9.5 mg
87169200	MASTERColour CDM-T Elite 100W/930 G12 1CT/12	101 kWh	10.1 mg	10.1 mg
87156200	MASTERColour CDM-T Elite 20W/830 G12.1CT/12	21 kWh	3.5 mg	3.5 mg
91137400	MasterC CDM-T Elite 35W/930 G12 1CT/12	40 kWh	4.7 mg	4.7 mg

Order Code	Full Product Name	Energy	Mercury	Mercury
		consumption kWh/1,000 hours	(Hg) content (max.)	(Hg) content (nom.)
16364000	MASTERColour CDM-T Elite 35W/942 G12 1CT	40 kWh	4.9 mg	4.9 mg
91141100	MASTERColour CDM-T Elite 70W/930 G12 1CT/12	74 kWh	6.6 mg	6.6 mg
16362600	MASTERColour CDM-T Elite 70W/942 G12 1CT	74 kWh	6.6 mg	6.6 mg
20159500	MASTERColour CDM-T Elite 50W/942 G12 1CT	51 kWh	5.7 mg	5.7 mg

MASTERColour CDM-T Elite

Order Code	Full Product Name	Energy	Mercury	Mercury
		consumption kWh/1,000 hours	(Hg) content (max.)	(Hg) content (nom.)
93060300	MASTERColour CDM-T Elite 50W/930 G12 1CT/12	51 kWh	6.6 mg	6.6 mg

