



产品描述

MASTERColour CDM-T 精锐型

单端高效陶瓷金属卤化物放电灯

优点

- 高流明输出和极高的显色性对商品有杰出的表现力，是促进商品销售的有力工具
- 在寿命周期内保持稳定出色的光色品质，维持店铺的统一形象
- 超高光效、超长寿命可以降低热辐射及店铺维护成本，提高店内环境的舒适度
- UV 防护，降低商品褪色风险

特点

- 清新纯净的白光
- 优异的显色性(Ra90)
- 整个寿命期间表现可靠
- 超级稳定的色彩表现,对红色表现优异(Ra=40)
- 相比普通陶瓷金卤灯光输出及流明维持率大幅提高

应用

- 商业连锁店铺情景及展示照明的最佳方案
- 室外装饰泛光照明
- 必须用在有前置玻璃的封闭式灯具(IEC 61167 and IEC60958)
- 推荐配套电子镇流器使用

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-T 精锐型

Versions



LPPR_CDM-T-E_100W_G12-Product photo




LPPR_CDM-T-E_0004-Product photo



LPPR_CDM-T-E_0006-Product photo

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 100W/930 G12 1CT/12	20 mm	8.5 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 50W/930 G12 1CT/12	20 mm	6 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm

一般信息	
底盖	G12
操作位置	UNIVERSAL
灯技术	
颜色名称	暖白色 (WW)
相关色温 (标称)	3000 K
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡外形	T19

灯技术

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	显色指数 (CRI)	光效 (额定)(标称)	光通量
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12	0.434	0.398	92	110 lm/W	11,000 lm
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	0.435	0.395	90	98 lm/W	-

MASTERColour CDM-T 精锐型

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	显色指数 (CRI)	光效 (额定)(标称)	光通量
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12	0.434	0.398	90	98 lm/W	4,050 lm
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	0.435	0.396	90	103 lm/W	-
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	0.434	0.398	90	103 lm/W	7,800 lm
928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12	0.434	0.398	90	108 lm/W	5,450 lm

操作和电气

Order Code	Full Product Name	电压 (标称)	功耗	Order Code	Full Product Name	电压 (标称)	功耗
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12	88 V	100.1 W	928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	85 V	73.2 W
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	85 V	39.1 W	928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	85 V	73.2 W
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12	85 V	39.1 W	928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12	90 V	50.2 W

审批和申请

Order Code	Full Product Name	能耗 kWh/ 1000 h	汞 (Hg) 含 量 (最高)	汞 (Hg) 含 量 (标称)
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12	101 kWh	10.1 mg	10.1 mg
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	43 kWh	-	4.7 mg
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12	40 kWh	4.7 mg	4.7 mg
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	80 kWh	-	6.6 mg
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	74 kWh	6.6 mg	6.6 mg
928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12	51 kWh	6.6 mg	6.6 mg

