



產品說明

MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

微型單端陶瓷複金屬燈。PGJ5 型一旋即緊燈座

优点

- 歷久如新的穩定光色
- 高效率燈具，節省電費支出，降低光照熱度
- 使用壽命優於鹵素燈。
- 熱度較其他燈具為低，使顧客與工作人員更感舒適
- 機械改裝鹵素燈泡 (GY6.35) 燈具 (相同發光中心長度)；如需整體改裝，安定器與燈座應一併更換
- 紫外線阻隔功能，減少商品褪色風險

特点

- 璀璨透亮的照明效果，營造舒適的氛圍
- 光照熱度低
- 清晰明亮的白色光
- 絕佳的演色性
- 極精巧型迷你燈具，光束強度高，用於近距離展示照明
- 構造堅固的旋緊型燈座，更換燈泡最容易
- 任何位置均可點燃

应用

- 強調與展示照明，展現清亮晶瑩效果
- 戶外裝飾泛光照明

MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

安全提示


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- For 20W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 20W
- For 35W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 35W
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CDM-Tm 0001

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-Tm	13.2 mm	0.44 in	3 mm	22.3 mm	22.9 mm	22.6	52 mm
Mini 20W/830 PGJ5						mm	
1CT/12							



MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

