



產品說明

MASTERColour CDM-T 陶瓷複金屬燈

精巧、高效率單端型放電式反射燈具系列，光色歷久如新，光線清晰明亮

优点

- 歷久如新的穩定光色
- 高效率燈具，節省電費支出，降低光照熱度
- 使用壽命優於白熾燈與鹵素燈
- 熱度較其他燈具為低，使顧客與工作人員更感舒適
- 所有型號皆配備紫外線阻隔功能，避免光照導致商品褪色

特点

- 清晰明亮的白色光
- 絕佳的演色性
- 小巧燈具也能展現高強度光束照明效果

应用

- 店面和商品櫥窗、辦公室與公共建築
- 戶外裝飾照明：泛光照明與行人徒步區

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



MASTERColour CDM-T 陶瓷複金屬燈

Versions



LPPR CDM-T 0005

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 250W/830 G12 1CT/12	25 mm	12.3 mm	71.5 mm	73.5 mm	72.5 mm	135 mm
MASTERC CDM-T 250W/942 G12 1CT/12	25 mm	12.3 mm	71.5 mm	73.5 mm	72.5 mm	135 mm

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 in	9 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 150W/942 G12 1CT	20 mm	0.75 in	8 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 35W/830 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T 35W/842 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T 70W/830 G12 1CT/12	20 mm	0.75 in	7 mm	55 mm	57 mm	56 mm	103 mm

一般資訊	
燈座基底	G12
操作位置	UNIVERSAL
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明

照明技術

MASTERColour CDM-T 陶瓷複金屬燈

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	色彩名稱	相關色溫 (標稱)	演色性指數 (CRI)	光效 (額定) (標準)	光通量
928083105129	MASTERC CDM-T 35W/830 G12 1CT/12	0.428	0.397	暖白光 (WW)	3000 K	83	79 lm/W	-
928094305129	MASTERC CDM-T 35W/842 G12 1CT/12	0.370	0.367	冷白光 (CW)	4200 K	84	77 lm/W	-
928082305129	MASTERC CDM-T 70W/830 G12 1CT/12	0.432	0.395	暖白光 (WW)	3000 K	84	85 lm/W	-
928083705125	MASTERC CDM-T 150W/830 G12 1CT	0.434	0.398	暖白光 (WW)	3000 K	88	88 lm/W	13,000 lm
928084605131	MASTERC CDM-T 150W/942 G12 1CT	0.371	0.366	冷白光 (CW)	4200 K	96	82 lm/W	12,100 lm
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	0.434	0.398	暖白光 (WW)	3000 K	85	111 lm/W	27,750 lm
928094205131	MASTERC CDM-T 250W/942 G12 1CT/12	0.371	0.366	冷白光 (CW)	4200 K	91	105 lm/W	26,250 lm

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量
928083105129	MASTERC CDM-T 35W/830 G12 1CT/12	82 V	39.1 W
928094305129	MASTERC CDM-T 35W/842 G12 1CT/12	85 V	39.1 W
928082305129	MASTERC CDM-T 70W/830 G12 1CT/12	88 V	73.2 W
928083705125	MASTERC CDM-T 150W/830 G12 1CT	96 V	150.1 W

Order Code	Full Product Name	電壓 (標稱)	耗電量
928084605131	MASTERC CDM-T 150W/942 G12 1CT	90 V	150.1 W
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	95 V	250.0 W
928094205131	MASTERC CDM-T 250W/942 G12 1CT/12	93 V	250.0 W


機械與外罩


Order Code	Full Product Name	燈泡形狀
928083105129	MASTERC CDM-T 35W/830 G12 1CT/12	T19
928094305129	MASTERC CDM-T 35W/842 G12 1CT/12	T19
928082305129	MASTERC CDM-T 70W/830 G12 1CT/12	T19
928083705125	MASTERC CDM-T 150W/830 G12 1CT	T19

Order Code	Full Product Name	燈泡形狀
928084605131	MASTERC CDM-T 150W/942 G12 1CT	T19
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	T24
928094205131	MASTERC CDM-T 250W/942 G12 1CT/12	T24



認證與應用


Order Code	Full Product Name	能源消耗 kWh/1000 h	汞 (Hg) 含 量 (最大)	汞 (Hg) 含量 (標稱)
928083105129	MASTERC CDM-T 35W/830 G12 1CT/12	43 kWh	-	3.1 mg
928094305129	MASTERC CDM-T 35W/842 G12 1CT/12	43 kWh	-	2.7 mg
928082305129	MASTERC CDM-T 70W/830 G12 1CT/12	80 kWh	-	4.6 mg
928083705125	MASTERC CDM-T 150W/830 G12 1CT	151 kWh	14.3 mg	14.3 mg
928084605131	MASTERC CDM-T 150W/942 G12 1CT	151 kWh	10.4 mg	10.4 mg
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	250 kWh	27.5 mg	27.5 mg
928094205131	MASTERC CDM-T 250W/942 G12 1CT/12	250 kWh	20 mg	20.0 mg





MASTERColour CDM-T 陶瓷複金屬燈





MASTERColour CDM-T 陶瓷複金屬燈

