



Product Description

MASTER HPI-T Plus

Quartz metal halide lamps with clear outer bulb

Benefits

- High safety and comfort level, maintained over life
- Minimal maintenance cost
- Initial investment saving options with "Plus"-concept

Features

- Clear tubular outer bulb
- Unique 3-band technology resulting in high luminous efficacy, both initially and over long lifetime
- Renders a natural white colour appearance and good colour stability

Application

- Sports lighting, floodlighting of buildings and monuments, area lighting e.g. harbours and building sites, canopy lighting e.g. petrol stations, horticultural lighting

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER HPI-T Plus

Versions



LPPR HPI-T

Dimensional drawing



Product	D (max)	O	L	C (max)
MASTER HPI-T Plus 400W/643 E39 1SL	47 mm	30.5 mm	165 mm	283 mm

