



Product Description

MASTER MHN-SE

Very compact quartz metal halide lamps with single-pin GX-22 lamp cap

Výhody

- Allows compact, highly efficient luminaire systems with high-precision optics for good beam control and minimal light spill
- Very good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers a superior solution for professional stadiums with regular TV coverage

Vlastnosti

- Single-pin concept for superior optical performance
- High luminous efficacy
- Natural white color appearance, very good color rendering and good color stability
- Daylight color temperature eases transition from daylight to artificial lighting

Aplikácie

- Professional sports lighting

Varovanie a ochrana

- Používajte len v úplne uzavretom svietidle, aj počas testovania (normy IEC61167, IEC62035, IEC60598).
- Svietidlo musí byť prispôbené na zachytenie horúcich častí, keď praskne svetelný zdroj.
- Je veľmi nepravdepodobné, že by rozbitie svetelného zdroja mohlo mať akýkoľvek vplyv na vaše zdravie. Ak sa svetelný zdroj rozbije, miestnosť 30 minút vetrajte a odstráňte časti svetelného zdroja, pokiaľ možno rukavicami. Vložte ich do utesneného plastového vrečka a odneste ich na recykláciu do miestneho zariadenia na nakladanie s odpadmi. Nepoužívajte vysávač.


MASTER MHN-SE

Versions



LPPR MHN-SE 0002

Rozmerový obrázok



Product	D (max)	O	C (max)
MASTER MHN-SE 2000W/956 GX22 400V HO UNP	41 mm	25 mm	198 mm

