



GreenUp deep recessed downlight G2: The most affordable deep recessed downlight

GreenUp deep recessed downlight G2

The GreenUp deep recessed downlight G2 line offers a selection of popular LED luminaires that not only capture the trend of deep recessed but also come with high levels of Philips quality at a competitive price. Reliable, energy-efficient and affordable—just what you need.

Benefits

- Philips quality and reliability
- Energy-efficient
- Comfortable, diffused light

Features


- 100–110 lm/W
- Deep recessed design
- Multiple sizes and light levels available
- Multiple color temperatures available

Application

- Offices
- Corridors
- Rest rooms

GreenUp deep recessed downlight G2





Versions



GreenUp deep recessed downlight G2

GreenUp deep recessed downlight G2

Dimensional drawing



GreenUp deep recessed downlight G2

| Light Technical | |
|-------------------------------------|---------------------------|
| Color rendering index (CRI) | 80 |
| Operating and Electrical | |
| Protection class IEC | Safety class II |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Optical cover type | Polycarbonate Diffuser |
| Housing Color | Black |
| Mech. impact protection code | IK03 |
| Ingress protection code | IP20 |
| Approval and Application | |
| Ambient temperature range | -20 to +40 °C |
| CE mark | Yes |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | -10% / +20% |

Light Technical

| Order Code | Full Product Name | Correlated Color | Luminous Efficacy | Luminous Flux |
|--------------|---------------------------------|-------------------|-------------------|---------------|
| | | Temperature (Nom) | (rated) (Nom) | |
| 911401565143 | DN035B D200 LED22/830 PSU WH G2 | 3000 K | 99 lm/W | 1,980 lm |
| 911401565243 | DN035B D200 LED22/840 PSU WH G2 | 4000 K | 110 lm/W | 2,200 lm |
| 911401565343 | DN035B D200 LED22/865 PSU WH G2 | 6500 K | 110 lm/W | 2,200 lm |
| 911401565443 | DN035B D200 LED32/830 PSU WH G2 | 3000 K | 99 lm/W | 2,880 lm |
| 911401565543 | DN035B D200 LED32/840 PSU WH G2 | 4000 K | 110 lm/W | 3,200 lm |
| 911401565643 | DN035B D200 LED32/865 PSU WH G2 | 6500 K | 110 lm/W | 3,200 lm |
| 911401563643 | DN035B D75 LED6/830 PSU WH G2 | 3000 K | 90 lm/W | 540 lm |
| 911401563743 | DN035B D75 LED6/840 PSU WH G2 | 4000 K | 100 lm/W | 600 lm |
| 911401563843 | DN035B D75 LED6/865 PSU WH G2 | 6500 K | 100 lm/W | 600 lm |
| 911401563943 | DN035B D100 LED6/830 PSU WH G2 | 3000 K | 90 lm/W | 558 lm |
| 911401564043 | DN035B D100 LED6/840 PSU WH G2 | 4000 K | 100 lm/W | 620 lm |
| 911401564143 | DN035B D100 LED6/865 PSU WH G2 | 6500 K | 100 lm/W | 620 lm |
| 911401564243 | DN035B D100 LED10/830 PSU WH G2 | 3000 K | 99 lm/W | 855 lm |
| 911401564343 | DN035B D100 LED10/840 PSU WH G2 | 4000 K | 110 lm/W | 950 lm |
| 911401564443 | DN035B D100 LED10/865 PSU WH G2 | 6500 K | 110 lm/W | 950 lm |
| 911401564543 | DN035B D150 LED16/830 PSU WH G2 | 3000 K | 99 lm/W | 1,440 lm |
| 911401564643 | DN035B D150 LED16/840 PSU WH G2 | 4000 K | 110 lm/W | 1,600 lm |
| 911401564743 | DN035B D150 LED16/865 PSU WH G2 | 6500 K | 110 lm/W | 1,600 lm |
| 911401564843 | DN035B D150 LED20/830 PSU WH G2 | 3000 K | 99 lm/W | 1,800 lm |
| 911401564943 | DN035B D150 LED20/840 PSU WH G2 | 4000 K | 110 lm/W | 2,000 lm |
| 911401565043 | DN035B D150 LED20/865 PSU WH G2 | 6500 K | 110 lm/W | 2,000 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------|-------------------|--------------|---------------------------------|-------------------|
| 911401565143 | DN035B D200 LED22/830 PSU WH G2 | 18 W | 911401565443 | DN035B D200 LED32/830 PSU WH G2 | 26 W |
| 911401565243 | DN035B D200 LED22/840 PSU WH G2 | 18 W | 911401565543 | DN035B D200 LED32/840 PSU WH G2 | 26 W |
| 911401565343 | DN035B D200 LED22/865 PSU WH G2 | 18 W | 911401565643 | DN035B D200 LED32/865 PSU WH G2 | 26 W |

GreenUp deep recessed downlight G2

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------|-------------------|
| 911401563643 | DN035B D75 LED6/830 PSU WH G2 | 5.5 W |
| 911401563743 | DN035B D75 LED6/840 PSU WH G2 | 5.5 W |
| 911401563843 | DN035B D75 LED6/865 PSU WH G2 | 5.5 W |
| 911401563943 | DN035B D100 LED6/830 PSU WH G2 | 6 W |
| 911401564043 | DN035B D100 LED6/840 PSU WH G2 | 6 W |
| 911401564143 | DN035B D100 LED6/865 PSU WH G2 | 6 W |
| 911401564243 | DN035B D100 LED10/830 PSU WH G2 | 8.5 W |
| 911401564343 | DN035B D100 LED10/840 PSU WH G2 | 8.5 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------|-------------------|
| 911401564443 | DN035B D100 LED10/865 PSU WH G2 | 8.5 W |
| 911401564543 | DN035B D150 LED16/830 PSU WH G2 | 13 W |
| 911401564643 | DN035B D150 LED16/840 PSU WH G2 | 13 W |
| 911401564743 | DN035B D150 LED16/865 PSU WH G2 | 13 W |
| 911401564843 | DN035B D150 LED20/830 PSU WH G2 | 16.5 W |
| 911401564943 | DN035B D150 LED20/840 PSU WH G2 | 16.5 W |
| 911401565043 | DN035B D150 LED20/865 PSU WH G2 | 16.5 W |

