



Simply great LED

Ledinaire SlimDownlight

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

Benefits

- Philips quality and reliability
- Energy saving
- A comfortable, diffuse surface of light



Features

- Multiple sizes and light levels available
- Multiple light colours available
- Ultra-slim design

Application

- Corridors
- Public toilets
- Waiting rooms

Dimensional drawing



Ledinaire SlimDownlight

Product details



General Information	
Driver included	Yes
Light source replaceable	No
Light Technical	
Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	80
Optic type	Beam angle 110°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Colour	White
Mech. impact protection code	IK03
Ingress protection code	IP20/40
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM)	0.7
Stroboscopic effect	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM≤5
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous efficacy (rated)	
		(nom.)	Luminous Flux
929003250632	DN065B G4 LED12/840 12W 220-240V D150 RD	100 lm/W	1,200 lm
929003250932	DN065B G4 LED20/840 19W 220-240V D200 RD	105 lm/W	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929003250632	DN065B G4 LED12/840 12W 220-240V D150 RD	12 W

Ledinaire SlimDownlight

Order Code	Full Product Name	Power Consumption
929003250932	DN065B G4 LED20/840 19W 220-240V D200	19 W
RD		

