



Full cut out size, Full CCT Range, Full lumen output, Recessed Installation

SmartBright Pro Downlight gen2

The SmartBright Pro Downlight comes offering reliable lighting performance with recessed installation, suitable for diversified applications. Full cut out size from D75 to D200, full CCT range covering 3000K, 4000K and 6500K, lumen output covers 400lm to 2000lm, eye comfort experience with low flicker lighting can attract you more with its elegant design.

Benefits

- Recessed Installation
- Elegant look & feel
- Eye comfort experience with low flicker lighting
- CB / EMC compliance product with Philips brand promise

Features

- Cut out: D75, D100, D125, D150, D175, D200
- 4 CCT: 3000K, 4000K and 6500K
- Input voltage is 220-240V
- PF0.9
- Efficacy: up to 110lm/W
- CRI80
- IP44(front)/IP20(back)
- lifetime: 50khrs @L70&Ta25°C
- Working temperature: -20°C to +40°C

SmartBright Pro Downlight gen2

Application

- Residential
- Hospitality
- Retail
- Shopping mall
- Hotels

