



For every project where light really matters. A slim fit

CoreLine SlimDownlight

CoreLine slimdownlight delivers on the CoreLine promise of innovative, easy-to-use and high-quality indoor LED downlights. The CoreLine slim downlight is an innovative range of recessed and surface-mounted luminaires. It is designed to provide uniform lighting across multiple application areas. With instant energy-savings and a longer lifetime, this is an environmentally friendly and cost-saving solution. Its MultiColorTemp feature offers a choice of two colour temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes in stock. Simple and easy installation means that our slim downlight fits the same size cut-out, while the minimal built-in depth of 34 mm makes this product an ideal space-saving solution, especially for projects with limited fitting space. InterAct Ready option with integrated wireless communications in this family is available, to be used with InterAct gateways, sensors and software.

Benefits

- MultiColorTemp option to change colour temperature on site and simplify product selection
- Energy-saving and longer lifetime to reduce overall operating costs
- Installations are surface-mounted with recessed covers
- Fits suspended ceilings with low space (product height < 50 mm)
- Surface of light effect creates a comfortable, uniform look

CoreLine SlimDownlight

Features

- MultiColorTemp feature: two colour temperature options in a single luminaire (3,000 K, 4,000 K)
- Recessed (DN145B) and surface-mounted versions (DN145C)
- Energy-efficient with a long lifespan: up to 100 lm/W and 50,000 hours @L70
- Push-in connector with through-wiring option
- Multiple light output options: 650/1,100/2,100 lumen
- Colour temperature: 3,000 K and 4,000 K
- Choice of drivers; DALI and wireless with Interact ready
- Total height (including driver): 34 mm recessed; 50 mm surface-mounted

Application

- Corridors
- Retail stores
- Reception areas
- Restrooms
- Technical rooms

Versions



Coreline SlimDownlight-DN145C 10S





Coreline SlimDownlight-DN145C 20S






Coreline SlimDownlight-DN145B 6S

Dimensional drawing



CoreLine SlimDownlight

Dimensional drawing



Product details

CoreLine SlimDownlight 2100lm
side view



CoreLine SlimDownlight Surface-mounted 2100lm



CoreLine SlimDownlight 2100lm
with PSU driver and easy
connector



CoreLine SlimDownlight

Product details

CoreLine SlimDownlight 2100lm



Philips CoreLine SlimDownlight
Surface DT02



Philips CoreLine SlimDownlight
Surface DT01



CoreLine SlimDownlight

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	Unit
Service Tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Colour rendering index (CRI)	>80
Optic type	Beam angle 90°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Controls and Dimming	
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Colour	White
Mech. impact protection code	IK02
Ingress protection code	IP20/44
Approval and Application	
Ambient temperature range	0 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM)	1
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
911401806380	DN145C LED10S/830 PSU II WH	LED10S
911401806480	DN145C LED10S/840 PSU II WH	LED10S
911401806580	DN145C LED20S/830 PSU II WH	LED20S
911401806680	DN145C LED20S/840 PSU II WH	LED20S
910500465903	DN145B LED20S/830 PSD-E II WH	LED20S
910500465904	DN145B LED20S/840 PSD-E II WH	LED20S
910505101197	DN145B LED20S/830 WIA-E WH	-
910505101198	DN145B LED20S/840 WIA-E WH	-
911401806180	DN145B LED20S/830 PSU II WH	LED20S
911401806280	DN145B LED20S/840 PSU II WH	LED20S
910500465901	DN145B LED10S/830 PSD-E II WH	LED10S
910500465902	DN145B LED10S/840 PSD-E II WH	LED10S
910505101196	DN145B LED10S/840 WIA-E WH	-
911401805980	DN145B LED10S/830 PSU II WH	LED10S
911401806080	DN145B LED10S/840 PSU II WH	LED10S
911401805880	DN145B LED6S/840 PSU II WH	LED6S

Light Technical

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Luminous efficacy (rated) (nom.)	Luminous Flux	Number of light sources
911401806380	DN145C LED10S/830 PSU II WH	3000 K	100 lm/W	1,100 lm	1
911401806480	DN145C LED10S/840 PSU II WH	4000 K	100 lm/W	1,100 lm	1

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Luminous efficacy (rated) (nom.)	Luminous Flux	Number of light sources
911401806580	DN145C LED20S/830 PSU II WH	3000 K	100 lm/W	2,100 lm	1
911401806680	DN145C LED20S/840 PSU II WH	4000 K	100 lm/W	2,100 lm	1

CoreLine SlimDownlight

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Luminous efficacy (rated) (nom.)	Luminous Flux	Number of light sources
910500465903	DN145B LED20S/830 PSD-E II WH	3000 K	93 lm/W	2,100 lm	1
910500465904	DN145B LED20S/840 PSD-E II WH	4000 K	93 lm/W	2,100 lm	1
910505101197	DN145B LED20S/830 WIA-E WH	3000 K	93 lm/W	2,100 lm	-
910505101198	DN145B LED20S/840 WIA-E WH	4000 K	93 lm/W	2,100 lm	-
911401806180	DN145B LED20S/830 PSU II WH	3000 K	100 lm/W	2,100 lm	1
911401806280	DN145B LED20S/840 PSU II WH	4000 K	100 lm/W	2,100 lm	1

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401806380	DN145C LED10S/830 PSU II WH	11 W
911401806480	DN145C LED10S/840 PSU II WH	11 W
911401806580	DN145C LED20S/830 PSU II WH	21 W
911401806680	DN145C LED20S/840 PSU II WH	21 W
910500465903	DN145B LED20S/830 PSD-E II WH	22.5 W
910500465904	DN145B LED20S/840 PSD-E II WH	22.5 W
910505101197	DN145B LED20S/830 WIA-E WH	22.5 W
910505101198	DN145B LED20S/840 WIA-E WH	22.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401806380	DN145C LED10S/830 PSU II WH	No
911401806480	DN145C LED10S/840 PSU II WH	No
911401806580	DN145C LED20S/830 PSU II WH	No
911401806680	DN145C LED20S/840 PSU II WH	No
910500465903	DN145B LED20S/830 PSD-E II WH	Yes
910500465904	DN145B LED20S/840 PSD-E II WH	Yes
910505101197	DN145B LED20S/830 WIA-E WH	Yes
910505101198	DN145B LED20S/840 WIA-E WH	Yes

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401806380	DN145C LED10S/830 PSU II WH	Opal
911401806480	DN145C LED10S/840 PSU II WH	Opal

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Luminous efficacy (rated) (nom.)	Luminous Flux	Number of light sources
910500465901	DN145B LED10S/830 PSD-E II WH	3000 K	85 lm/W	1,100 lm	1
910500465902	DN145B LED10S/840 PSD-E II WH	4000 K	85 lm/W	1,100 lm	1
910505101196	DN145B LED10S/840 WIA-E WH	4000 K	93 lm/W	1,100 lm	-
911401805980	DN145B LED10S/830 PSU II WH	3000 K	100 lm/W	1,100 lm	1
911401806080	DN145B LED10S/840 PSU II WH	4000 K	100 lm/W	1,100 lm	1
911401805880	DN145B LED6S/840 PSU II WH	4000 K	100 lm/W	650 lm	1

Order Code	Full Product Name	Power Consumption
911401806180	DN145B LED20S/830 PSU II WH	21 W
911401806280	DN145B LED20S/840 PSU II WH	21 W
910500465901	DN145B LED10S/830 PSD-E II WH	13 W
910500465902	DN145B LED10S/840 PSD-E II WH	13 W
910505101196	DN145B LED10S/840 WIA-E WH	13 W
911401805980	DN145B LED10S/830 PSU II WH	11 W
911401806080	DN145B LED10S/840 PSU II WH	11 W
911401805880	DN145B LED6S/840 PSU II WH	6.5 W

Order Code	Full Product Name	Dimmable
911401806180	DN145B LED20S/830 PSU II WH	No
911401806280	DN145B LED20S/840 PSU II WH	No
910500465901	DN145B LED10S/830 PSD-E II WH	Yes
910500465902	DN145B LED10S/840 PSD-E II WH	Yes
910505101196	DN145B LED10S/840 WIA-E WH	Yes
911401805980	DN145B LED10S/830 PSU II WH	No
911401806080	DN145B LED10S/840 PSU II WH	No
911401805880	DN145B LED6S/840 PSU II WH	No

Order Code	Full Product Name	Optical cover type
911401806580	DN145C LED20S/830 PSU II WH	Opal
911401806680	DN145C LED20S/840 PSU II WH	Opal

CoreLine SlimDownlight

Order Code	Full Product Name	Optical cover type
910500465903	DN145B LED20S/830 PSD-E II WH	Opal
910500465904	DN145B LED20S/840 PSD-E II WH	Opal
910505101197	DN145B LED20S/830 WIA-E WH	-
910505101198	DN145B LED20S/840 WIA-E WH	-
911401806180	DN145B LED20S/830 PSU II WH	Opal
911401806280	DN145B LED20S/840 PSU II WH	Opal

Approval and Application

Order Code	Full Product Name	Stroboscopic effect
911401806380	DN145C LED10S/830 PSU II WH	1.6
911401806480	DN145C LED10S/840 PSU II WH	1.6
911401806580	DN145C LED20S/830 PSU II WH	1.6
911401806680	DN145C LED20S/840 PSU II WH	1.6
910500465903	DN145B LED20S/830 PSD-E II WH	0.4
910500465904	DN145B LED20S/840 PSD-E II WH	0.4
910505101197	DN145B LED20S/830 WIA-E WH	0.4
910505101198	DN145B LED20S/840 WIA-E WH	0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401806380	DN145C LED10S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806480	DN145C LED10S/840 PSU II WH	(0.38212,0.38031) SDCM<3
911401806580	DN145C LED20S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806680	DN145C LED20S/840 PSU II WH	(0.38212,0.38031) SDCM<3
910500465903	DN145B LED20S/830 PSD-E II WH	(0.43657,0.40454) SDCM<3
910500465904	DN145B LED20S/840 PSD-E II WH	(0.38212,0.38031) SDCM<3
910505101197	DN145B LED20S/830 WIA-E WH	(0.43657,0.40454) SDCM<3
910505101198	DN145B LED20S/840 WIA-E WH	(0.38212,0.38031) SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5,000 hours
911401806380	DN145C LED10S/830 PSU II WH	0.0015 %
911401806480	DN145C LED10S/840 PSU II WH	0.0015 %
911401806580	DN145C LED20S/830 PSU II WH	0.0015 %
911401806680	DN145C LED20S/840 PSU II WH	0.0015 %
910500465903	DN145B LED20S/830 PSD-E II WH	0.0015 %
910500465904	DN145B LED20S/840 PSD-E II WH	0.0015 %
910505101197	DN145B LED20S/830 WIA-E WH	-
910505101198	DN145B LED20S/840 WIA-E WH	-

Product Data

Order Code	Full Product Name	Product family code
911401806380	DN145C LED10S/830 PSU II WH	-
911401806480	DN145C LED10S/840 PSU II WH	-
911401806580	DN145C LED20S/830 PSU II WH	-
911401806680	DN145C LED20S/840 PSU II WH	-
910500465903	DN145B LED20S/830 PSD-E II WH	DN145B

Order Code	Full Product Name	Optical cover type
910500465901	DN145B LED10S/830 PSD-E II WH	Opal
910500465902	DN145B LED10S/840 PSD-E II WH	Opal
910505101196	DN145B LED10S/840 WIA-E WH	-
911401805980	DN145B LED10S/830 PSU II WH	Opal
911401806080	DN145B LED10S/840 PSU II WH	Opal
911401805880	DN145B LED6S/840 PSU II WH	Opal

Order Code	Full Product Name	Stroboscopic effect
911401806180	DN145B LED20S/830 PSU II WH	1.6
911401806280	DN145B LED20S/840 PSU II WH	1.6
910500465901	DN145B LED10S/830 PSD-E II WH	0.4
910500465902	DN145B LED10S/840 PSD-E II WH	0.4
910505101196	DN145B LED10S/840 WIA-E WH	0.4
911401805980	DN145B LED10S/830 PSU II WH	1.6
911401806080	DN145B LED10S/840 PSU II WH	1.6
911401805880	DN145B LED6S/840 PSU II WH	1.6

Order Code	Full Product Name	Initial chromaticity
911401806180	DN145B LED20S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806280	DN145B LED20S/840 PSU II WH	(0.38212,0.38031) SDCM<3
910500465901	DN145B LED10S/830 PSD-E II WH	(0.43657,0.40454) SDCM<3
910500465902	DN145B LED10S/840 PSD-E II WH	(0.38212,0.38031) SDCM<3
910505101196	DN145B LED10S/840 WIA-E WH	(0.38212,0.38031) SDCM<3
911401805980	DN145B LED10S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806080	DN145B LED10S/840 PSU II WH	(0.38212,0.38031) SDCM<3
911401805880	DN145B LED6S/840 PSU II WH	(0.38212,0.38031) SDCM<3

Order Code	Full Product Name	Driver failure rate at 5,000 hours
911401806180	DN145B LED20S/830 PSU II WH	0.0015 %
911401806280	DN145B LED20S/840 PSU II WH	0.0015 %
910500465901	DN145B LED10S/830 PSD-E II WH	0.0015 %
910500465902	DN145B LED10S/840 PSD-E II WH	0.0015 %
910505101196	DN145B LED10S/840 WIA-E WH	-
911401805980	DN145B LED10S/830 PSU II WH	0.0015 %
911401806080	DN145B LED10S/840 PSU II WH	0.0015 %
911401805880	DN145B LED6S/840 PSU II WH	-




Order Code	Full Product Name	Product family code
910500465904	DN145B LED20S/840 PSD-E II WH	DN145B
910505101197	DN145B LED20S/830 WIA-E WH	DN145B
910505101198	DN145B LED20S/840 WIA-E WH	DN145B
911401806180	DN145B LED20S/830 PSU II WH	-
911401806280	DN145B LED20S/840 PSU II WH	-

CoreLine SlimDownlight

Order Code	Full Product Name	Product family code
910500465901	DN145B LED10S/830 PSD-E II WH	DN145B
910500465902	DN145B LED10S/840 PSD-E II WH	DN145B
910505101196	DN145B LED10S/840 WIA-E WH	DN145B

Order Code	Full Product Name	Product family code
911401805980	DN145B LED10S/830 PSU II WH	-
911401806080	DN145B LED10S/840 PSU II WH	-
911401805880	DN145B LED6S/840 PSU II WH	-




Polar Wide Diagrams



Polar Normal (separate) - DN145BI - 910500465901

Polar Normal (separate) - DN145BI - 910500465903




Polar Normal (separate) - DN145BI - 910500465904



Polar Normal (separate) - DN145BI - 910500465902

Polar Normal (separate) - DN145BI - 910505101196

Polar Normal (separate) - DN145BI - 910505101198






Polar Normal (separate) - DN145BI - 910505101197

Polar Normal (separate) - null - 911401805880

Polar Normal (separate) - null - 911401805980




Polar Wide Diagrams



Polar Normal (separate) - null - 911401806080

Polar Normal (separate) - null - 911401806180


Polar Normal (separate) - null - 911401806280



Polar Normal (separate) - null - 911401806380

Polar Normal (separate) - null - 911401806580

Polar Normal (separate) - null - 911401806680



Polar Normal (separate) - null - 911401806480

