



For every project where light really matters. A slim fit

CoreLine SlimDownlight

CoreLine slimdownlight delivers on the CoreLine promise of innovative, easy to use and high-quality indoor LED downlights. CoreLine slimdownlight is an innovative range of recessed and surface-mounted luminaires. It is designed to provide uniform lighting across multiple application areas. With instant energy savings and a longer lifetime, this is an environmentally friendly and cost saving solution. Its MultiColorTemp feature offers a choice of two color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Simple and easy installation means our slim downlight fits the same size cut-out, while the minimal built-in depth of 34mm makes this product an ideal space saving solution, especially for projects with limited fitting space. InterAct Ready option with integrated wireless communications in this family is available, to be used with InterAct gateways, sensors and software.

Benefits

- MultiColorTemp option to change color temperature on site and simplify product selection
- Energy saving and longer lifetime to reduce overall operating costs
- Covers recessed and surface-mounted installations
- Fits suspended ceilings with low space (Product height < 50mm)
- Surface of light effect creates a comfortable, uniform look

CoreLine SlimDownlight

Features

- MultiColorTemp feature: two color temperature options in a single luminaire (3000K-4000K)
- Recessed (DN145B) and surface-mounted versions (DN145C)
- Energy-efficient with a long lifespan: up to 100lm/W and 50,000 hours @L70
- Push-in connector with through-wiring option
- Multiple light output options: 650/1100/2100 lumen
- Color temperature: 3000K and 4000K
- Choice of drivers; DALI and wireless with Interact ready
- Total height (including driver): 34mm recessed; 50mm surface mounted

Application

- Corridors
- Retail stores
- Reception areas
- Restrooms
- Technical rooms

Versions





Coreline SlimDownlight-DN145C 20S





Coreline SlimDownlight-DN145B 20S

Dimensional drawing



CoreLine SlimDownlight

Dimensional drawing



Product details

CoreLine SlimDownlight 2100lm
side view



CoreLine SlimDownlight Surface-mounted 2100lm



CoreLine SlimDownlight 2100lm
with PSU driver and easy
connector



CoreLine SlimDownlight 2100lm



Philips CoreLine SlimDownlight
Surface DT02



Philips CoreLine SlimDownlight
Surface DT01



CoreLine SlimDownlight

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Number of light sources	1
Optic type	Beam angle 90°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Controls and Dimming	
Maximum dim level	Not applicable
Mechanical and Housing	
Optical cover type	Opal
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20/44
Approval and Application	
Ambient temperature range	0 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.0015 %

General Information

Order Code	Full Product Name	Lamp family code
911401806380	DN145C LED10S/830 PSU II WH	LED10S
911401806480	DN145C LED10S/840 PSU II WH	LED10S
911401806580	DN145C LED20S/830 PSU II WH	LED20S
911401806680	DN145C LED20S/840 PSU II WH	LED20S
910500465903	DN145B LED20S/830 PSD-E II WH	LED20S
910500465904	DN145B LED20S/840 PSD-E II WH	LED20S
911401806180	DN145B LED20S/830 PSU II WH	LED20S
911401806280	DN145B LED20S/840 PSU II WH	LED20S
910500465902	DN145B LED10S/840 PSD-E II WH	LED10S
911401805980	DN145B LED10S/830 PSU II WH	LED10S
911401806080	DN145B LED10S/840 PSU II WH	LED10S

Light Technical

CoreLine SlimDownlight

Order Code	Full Product Name	Correlated Color	Luminous	Luminous
		Temperature	Efficacy (rated)	
		(Nom)	(Nom)	Flux
911401806380	DN145C LED10S/830 PSU II WH	3000 K	100 lm/W	1,100 lm
911401806480	DN145C LED10S/840 PSU II WH	4000 K	100 lm/W	1,100 lm
911401806580	DN145C LED20S/830 PSU II WH	3000 K	100 lm/W	2,100 lm
911401806680	DN145C LED20S/840 PSU II WH	4000 K	100 lm/W	2,100 lm
910500465903	DN145B LED20S/830 PSD-E II WH	3000 K	93 lm/W	2,100 lm
910500465904	DN145B LED20S/840 PSD-E II WH	4000 K	93 lm/W	2,100 lm

Order Code	Full Product Name	Correlated Color	Luminous	Luminous
		Temperature	Efficacy (rated)	
		(Nom)	(Nom)	Flux
911401806180	DN145B LED20S/830 PSU II WH	3000 K	100 lm/W	2,100 lm
911401806280	DN145B LED20S/840 PSU II WH	4000 K	100 lm/W	2,100 lm
910500465902	DN145B LED10S/840 PSD-E II WH	4000 K	85 lm/W	1,100 lm
911401805980	DN145B LED10S/830 PSU II WH	3000 K	100 lm/W	1,100 lm
911401806080	DN145B LED10S/840 PSU II WH	4000 K	100 lm/W	1,100 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401806380	DN145C LED10S/830 PSU II WH	11 W
911401806480	DN145C LED10S/840 PSU II WH	11 W
911401806580	DN145C LED20S/830 PSU II WH	21 W
911401806680	DN145C LED20S/840 PSU II WH	21 W
910500465903	DN145B LED20S/830 PSD-E II WH	22.5 W
910500465904	DN145B LED20S/840 PSD-E II WH	22.5 W

Order Code	Full Product Name	Power Consumption
911401806180	DN145B LED20S/830 PSU II WH	21 W
911401806280	DN145B LED20S/840 PSU II WH	21 W
910500465902	DN145B LED10S/840 PSD-E II WH	13 W
911401805980	DN145B LED10S/830 PSU II WH	11 W
911401806080	DN145B LED10S/840 PSU II WH	11 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401806380	DN145C LED10S/830 PSU II WH	No
911401806480	DN145C LED10S/840 PSU II WH	No
911401806580	DN145C LED20S/830 PSU II WH	No
911401806680	DN145C LED20S/840 PSU II WH	No
910500465903	DN145B LED20S/830 PSD-E II WH	Yes
910500465904	DN145B LED20S/840 PSD-E II WH	Yes

Order Code	Full Product Name	Dimmable
911401806180	DN145B LED20S/830 PSU II WH	No
911401806280	DN145B LED20S/840 PSU II WH	No
910500465902	DN145B LED10S/840 PSD-E II WH	Yes
911401805980	DN145B LED10S/830 PSU II WH	No
911401806080	DN145B LED10S/840 PSU II WH	No

Approval and Application

Order Code	Full Product Name	Stroboscopic effect visibility
		measure (SVM)
911401806380	DN145C LED10S/830 PSU II WH	1.6
911401806480	DN145C LED10S/840 PSU II WH	1.6
911401806580	DN145C LED20S/830 PSU II WH	1.6
911401806680	DN145C LED20S/840 PSU II WH	1.6
910500465903	DN145B LED20S/830 PSD-E II WH	0.4
910500465904	DN145B LED20S/840 PSD-E II WH	0.4

Order Code	Full Product Name	Stroboscopic effect visibility
		measure (SVM)
911401806180	DN145B LED20S/830 PSU II WH	1.6
911401806280	DN145B LED20S/840 PSU II WH	1.6
910500465902	DN145B LED10S/840 PSD-E II WH	0.4
911401805980	DN145B LED10S/830 PSU II WH	1.6
911401806080	DN145B LED10S/840 PSU II WH	1.6

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401806380	DN145C LED10S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806480	DN145C LED10S/840 PSU II WH	(0.38212,0.38031) SDCM<3
911401806580	DN145C LED20S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806680	DN145C LED20S/840 PSU II WH	(0.38212,0.38031) SDCM<3
910500465903	DN145B LED20S/830 PSD-E II WH	(0.43657,0.40454) SDCM<3
910500465904	DN145B LED20S/840 PSD-E II WH	(0.38212,0.38031) SDCM<3




Order Code	Full Product Name	Initial chromaticity
911401806180	DN145B LED20S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806280	DN145B LED20S/840 PSU II WH	(0.38212,0.38031) SDCM<3
910500465902	DN145B LED10S/840 PSD-E II WH	(0.38212,0.38031) SDCM<3
911401805980	DN145B LED10S/830 PSU II WH	(0.43657,0.40454) SDCM<3
911401806080	DN145B LED10S/840 PSU II WH	(0.38212,0.38031) SDCM<3

Product Data


Order Code	Full Product Name	Product family code
911401806380	DN145C LED10S/830 PSU II WH	-
911401806480	DN145C LED10S/840 PSU II WH	-
911401806580	DN145C LED20S/830 PSU II WH	-
911401806680	DN145C LED20S/840 PSU II WH	-
910500465903	DN145B LED20S/830 PSD-E II WH	DN145B
910500465904	DN145B LED20S/840 PSD-E II WH	DN145B

Order Code	Full Product Name	Product family code
911401806180	DN145B LED20S/830 PSU II WH	-
911401806280	DN145B LED20S/840 PSU II WH	-
910500465902	DN145B LED10S/840 PSD-E II WH	DN145B
911401805980	DN145B LED10S/830 PSU II WH	-
911401806080	DN145B LED10S/840 PSU II WH	-


Polar Wide Diagrams




Polar Normal (separate) - DN145BI - 910500465903



Polar Normal (separate) - DN145BI - 910500465904



Polar Normal (separate) - DN145BI - 910500465902






Polar Normal (separate) - null - 911401805980

Polar Normal (separate) - null - 911401806080

Polar Normal (separate) - null - 911401806180



Polar Wide Diagrams



Polar Normal (separate) - null - 911401806280

Polar Normal (separate) - null - 911401806380

Polar Normal (separate) - null - 911401806580



Polar Normal (separate) - null - 911401806680

Polar Normal (separate) - null - 911401806480

