



LuxSpace Pro – high efficiency, visual comfort and a stylish design

LuxSpace Pro

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Benefits

- Energy-efficient LED
- Creates a gentle, natural light, ensuring visual comfort
- Perfect ceiling integration with narrow rim
- Option of glossy faceted & matte clear aluminized (UGR19), or faceted & matte white reflector
- Durable LED quality and reliability
- Supports Human Centric Lighting with Tunable White and integrated lighting controls

Features

- Best-in-class efficacy with up to 170lm/W
- Deep recessed architecture with increased reflector depth
- Spacious installation area with improved narrow rim width
- Choice of multiple optics: Facetted, matt and white
- 75,000 hours lifetime @L70/B50 Ta 25°C
- 50,000 hours lifetime @L80/B10 Ta 25°C
- DALI and wireless Interact compatible

Application





- Retail
- Offices
- Hospitals and Care Centers
- Hospitality
- Airports
- Exhibition Center

Versions




LuxSpace Pro

Dimensional drawing



Dimensional drawing



General Information	
Service tag	Yes
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	Polycarbonate Diffuser
Housing Color	White
Mech. impact protection code	IK03
Approval and Application	
Ambient temperature range	-20 °C to 40 °C
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color	Color	Luminous	Luminous Flux
		Temperature	rendering	Efficacy (rated)	
		(Nom)	index (CRI)	(Nom)	
911401502944	DN589B LED10/840 P8PSU D100 WB WP G2	4000 K	80	128 lm/W	1,073 lm
911401591243	DN588B LED5/930 P4PSU D100 WB G2	3000 K	90	110 lm/W	453 lm
911401591343	DN588B LED5/940 P4PSU D100 WB G2	4000 K	90	115 lm/W	478 lm
911401591443	DN589B LED10/930 P8PSU D100 WB G2	3000 K	90	116 lm/W	971 lm
911401591543	DN589B LED10/940 P8PSU D100 WB G2	4000 K	90	122 lm/W	1,023 lm
911401591643	DN590B LED16/930 P13PSU D100 WB G2	3000 K	90	111 lm/W	1,494 lm
911401591743	DN590B LED16/940 P13PSU D100 WB G2	4000 K	90	117 lm/W	1,574 lm
911401591843	DN589B LED10/930 P8PSD D100 WB G2	3000 K	90	118 lm/W	889 lm
911401591943	DN589B LED10/940 P8PSD D100 WB G2	4000 K	90	124 lm/W	937 lm
911401592043	DN590B LED16/930 P14PSD D100 WB G2	3000 K	90	107 lm/W	1,494 lm
911401592143	DN590B LED16/940 P14PSD D100 WB G2	4000 K	90	113 lm/W	1,574 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401592243	DN589X LED10/940 P9WIA D100 WB G2	4000 K	90	117 lm/W	1,023 lm
911401592343	DN590X LED16/940 P14WIA D100 WB G2	4000 K	90	115 lm/W	1,574 lm
911401500044	DN596B LED80/830 P62PSU D200 WB G2	3000 K	80	124 lm/W	7,654 lm
911401500144	DN596B LED80/840 P62PSU D200 WB G2	4000 K	80	130 lm/W	7,977 lm
911401500444	DN596B LED80/830 P59PSD D200 WB G2	3000 K	80	121 lm/W	7,124 lm
911401500544	DN596B LED80/840 P59PSD D200 WB G2	4000 K	80	126 lm/W	7,425 lm
911401500844	DN591B LED19/830 P13PSU D200 WB G2	3000 K	80	143 lm/W	1,828 lm
911401500944	DN591B LED19/840 P13PSU D200 WB G2	4000 K	80	149 lm/W	1,905 lm
911401501244	DN591B LED19/830 P13PSD D200 WB G2	3000 K	80	138 lm/W	1,828 lm
911401501344	DN591B LED19/840 P13PSD D200 WB G2	4000 K	80	144 lm/W	1,905 lm
911401501544	DN591X LED19/840 P13WIA D200 WB G2	4000 K	80	147 lm/W	1,905 lm
911401501844	DN593B LED29/830 P20PSU D200 WB G2	3000 K	80	141 lm/W	2,825 lm
911401501944	DN593B LED29/840 P20PSU D200 WB G2	4000 K	80	146 lm/W	2,944 lm
911401502244	DN593B LED29/830 P21PSD D200 WB G2	3000 K	80	136 lm/W	2,825 lm
911401502344	DN593B LED29/840 P21PSD D200 WB G2	4000 K	80	141 lm/W	2,944 lm
911401502844	DN591B LED23/840 P13PSU D200 WB UE G2	4000 K	80	173 lm/W	2,279 lm
911401598243	DN594B LED42/830 P30PSU D200 WB G2	3000 K	80	136 lm/W	4,050 lm
911401598343	DN594B LED42/840 P30PSU D200 WB G2	4000 K	80	142 lm/W	4,221 lm
911401598643	DN594B LED42/830 P31PSD D200 WB G2	3000 K	80	132 lm/W	4,050 lm
911401598743	DN594B LED42/840 P31PSD D200 WB G2	4000 K	80	137 lm/W	4,221 lm
911401598943	DN594X LED42/840 P30WIA D200 WB G2	4000 K	80	142 lm/W	4,221 lm
911401599343	DN595B LED61/840 P46PSU D200 WB G2	4000 K	80	134 lm/W	6,116 lm
911401599643	DN595B LED61/830 P47PSD D200 WB G2	3000 K	80	126 lm/W	5,868 lm
911401599743	DN595B LED61/840 P47PSD D200 WB G2	4000 K	80	131 lm/W	6,116 lm
911401500244	DN596B LED80/830 P59PSD D200 VWB-M G2	3000 K	80	124 lm/W	7,298 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401500344	DN596B LED80/840 P59PSD D200 VWB-M G2	4000 K	80	129 lm/W	7,606 lm
911401500644	DN591B LED19/830 P13PSU D200 VWB-M G2	3000 K	80	146 lm/W	1,872 lm
911401500744	DN591B LED19/840 P13PSU D200 VWB-M G2	4000 K	80	153 lm/W	1,951 lm
911401501044	DN591B LED19/830 P13PSD D200 VWB-M G2	3000 K	80	141 lm/W	1,872 lm
911401501144	DN591B LED19/840 P13PSD D200 VWB-M G2	4000 K	80	147 lm/W	1,951 lm
911401501444	DN591X LED19/840 P13WIA D200 VWB-M G2	4000 K	80	151 lm/W	1,951 lm
911401501644	DN593B LED29/830 P20PSU D200 VWB-M G2	3000 K	80	144 lm/W	2,894 lm
911401501744	DN593B LED29/840 P20PSU D200 VWB-M G2	4000 K	80	150 lm/W	3,016 lm
911401502044	DN593B LED29/830 P21PSD D200 VWB-M G2	3000 K	80	139 lm/W	2,894 lm
911401502144	DN593B LED29/840 P21PSD D200 VWB-M G2	4000 K	80	145 lm/W	3,016 lm
911401502744	DN591B LED23/840 P13PSU D200 VWB-M UE G2	4000 K	80	177 lm/W	2,332 lm
911401598043	DN594B LED42/830 P30PSU D200 VWB-M G2	3000 K	80	140 lm/W	4,149 lm
911401598143	DN594B LED42/840 P30PSU D200 VWB-M G2	4000 K	80	146 lm/W	4,324 lm
911401598443	DN594B LED42/830 P31PSD D200 VWB-M G2	3000 K	80	135 lm/W	4,149 lm
911401598543	DN594B LED42/840 P31PSD D200 VWB-M G2	4000 K	80	141 lm/W	4,324 lm
911401598843	DN594X LED42/840 P30WIA D200 VWB-M G2	4000 K	80	146 lm/W	4,324 lm
911401599043	DN595B LED61/830 P46PSU D200 VWB-M G2	3000 K	80	132 lm/W	6,011 lm
911401599443	DN595B LED61/830 P47PSD D200 VWB-M G2	3000 K	80	129 lm/W	6,011 lm
911401599543	DN595B LED61/840 P47PSD D200 VWB-M G2	4000 K	80	134 lm/W	6,265 lm
911401599843	DN596B LED80/830 P62PSU D200 VWB-M G2	3000 K	80	127 lm/W	7,841 lm
911401599943	DN596B LED80/840 P62PSU D200 VWB-M G2	4000 K	80	133 lm/W	8,172 lm
911401502544	DN589B LED12/840 P7PSU D125 WB UE G2	4000 K	80	158 lm/W	1,185 lm
911401503044	DN590B LED17/840 P13PSU D125 WB WP G2	4000 K	80	131 lm/W	1,741 lm
911401592643	DN588B LED9/830 P6PSU D125 WB G2	3000 K	80	129 lm/W	837 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401592743	DN588B LED9/840 P6PSU D125 WB G2	4000 K	80	134 lm/W	872 lm
911401593043	DN589B LED11/830 P8PSU D125 WB G2	3000 K	80	130 lm/W	1,070 lm
911401593143	DN589B LED11/840 P8PSU D125 WB G2	4000 K	80	135 lm/W	1,116 lm
911401593443	DN589B LED11/830 P8PSD D125 WB G2	3000 K	80	122 lm/W	970 lm
911401593543	DN589B LED11/840 P8PSD D125 WB G2	4000 K	80	127 lm/W	1,011 lm
911401593843	DN590B LED17/830 P13PSU D125 WB G2	3000 K	80	126 lm/W	1,670 lm
911401593943	DN590B LED17/840 P13PSU D125 WB G2	4000 K	80	131 lm/W	1,741 lm
911401594243	DN590B LED17/830 P14PSD D125 WB G2	3000 K	80	121 lm/W	1,670 lm
911401594343	DN590B LED17/840 P14PSD D125 WB G2	4000 K	80	126 lm/W	1,741 lm
911401594643	DN591B LED22/830 P17PSU D125 WB G2	3000 K	80	125 lm/W	2,127 lm
911401594743	DN591B LED22/840 P17PSU D125 WB G2	4000 K	80	130 lm/W	2,216 lm
911401595043	DN591B LED22/830 P18PSD D125 WB G2	3000 K	80	120 lm/W	2,127 lm
911401595143	DN591B LED22/840 P18PSD D125 WB G2	4000 K	80	125 lm/W	2,216 lm
911401595343	DN591X LED22/840 P17WIA D125 WB G2	4000 K	80	130 lm/W	2,216 lm
911401595643	DN592B LED26/830 P21PSU D125 WB G2	3000 K	80	119 lm/W	2,529 lm
911401595743	DN592B LED26/840 P21PSU D125 WB G2	4000 K	80	125 lm/W	2,636 lm
911401596043	DN592B LED26/830 P22PSD D125 WB G2	3000 K	80	115 lm/W	2,529 lm
911401596143	DN592B LED26/840 P22PSD D125 WB G2	4000 K	80	120 lm/W	2,636 lm
911401596343	DN592X LED26/840 P21WIA D125 WB G2	4000 K	80	125 lm/W	2,636 lm
911401588543	DN588B LED5/930 P4PSU D75 NB G2	3000 K	90	100 lm/W	419 lm
911401588643	DN588B LED5/940 P4PSU D75 NB G2	4000 K	90	107 lm/W	449 lm
911401588743	DN588B LED5/930 P4PSU D75 MB G2	3000 K	90	100 lm/W	419 lm
911401588843	DN588B LED5/940 P4PSU D75 MB G2	4000 K	90	107 lm/W	449 lm
911401588943	DN588B LED5/930 P4PSU D75 WB G2	3000 K	90	100 lm/W	419 lm
911401589043	DN588B LED5/940 P4PSU D75 WB G2	4000 K	90	107 lm/W	449 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401589143	DN589B LED10/930 P8PSU D75 NB G2	3000 K	90	109 lm/W	922 lm
911401589243	DN589B LED10/940 P8PSU D75 NB G2	4000 K	90	116 lm/W	988 lm
911401589343	DN589B LED10/930 P8PSU D75 MB G2	3000 K	90	109 lm/W	922 lm
911401589443	DN589B LED10/940 P8PSU D75 MB G2	4000 K	90	116 lm/W	988 lm
911401589543	DN589B LED10/930 P8PSU D75 WB G2	3000 K	90	109 lm/W	922 lm
911401589643	DN589B LED10/940 P8PSU D75 WB G2	4000 K	90	116 lm/W	988 lm
911401589743	DN590B LED15/930 P14PSU D75 NB G2	3000 K	90	103 lm/W	1,406 lm
911401589843	DN590B LED15/940 P14PSU D75 NB G2	4000 K	90	110 lm/W	1,506 lm
911401589943	DN590B LED15/930 P14PSU D75 MB G2	3000 K	90	103 lm/W	1,406 lm
911401590043	DN590B LED15/940 P14PSU D75 MB G2	4000 K	90	110 lm/W	1,506 lm
911401590143	DN590B LED15/930 P14PSU D75 WB G2	3000 K	90	103 lm/W	1,406 lm
911401590243	DN590B LED15/940 P14PSU D75 WB G2	4000 K	90	110 lm/W	1,506 lm
911401590343	DN590B LED15/930 P14PSD D75 NB G2	3000 K	90	99 lm/W	1,406 lm
911401590443	DN590B LED15/940 P14PSD D75 NB G2	4000 K	90	107 lm/W	1,506 lm
911401590543	DN590B LED15/930 P14PSD D75 MB G2	3000 K	90	99 lm/W	1,406 lm
911401590643	DN590B LED15/940 P14PSD D75 MB G2	4000 K	90	107 lm/W	1,506 lm
911401590743	DN590B LED15/930 P14PSD D75 WB G2	3000 K	90	99 lm/W	1,406 lm
911401590843	DN590B LED15/940 P14PSD D75 WB G2	4000 K	90	107 lm/W	1,506 lm
911401590943	DN590X LED15/940 P14WIA D75 NB G2	4000 K	90	109 lm/W	1,506 lm
911401591043	DN590X LED15/940 P14WIA D75 MB G2	4000 K	90	109 lm/W	1,506 lm
911401591143	DN590X LED15/940 P14WIA D75 WB G2	4000 K	90	109 lm/W	1,506 lm
911401502444	DN589B LED12/840 P7PSU D125 VWB-M UE G2	4000 K	80	162 lm/W	1,214 lm
911401592443	DN588B LED9/830 P6PSU D125 VWB-M G2	3000 K	80	132 lm/W	858 lm
911401592543	DN588B LED9/840 P6PSU D125 VWB-M G2	4000 K	80	138 lm/W	895 lm
911401592843	DN589B LED11/830 P8PSU D125 VWB-M G2	3000 K	80	133 lm/W	1,098 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401592943	DN589B LED11/840 P8PSU D125 VWB-M G2	4000 K	80	139 lm/W	1,144 lm
911401593243	DN589B LED11/830 P8PSD D125 VWB-M G2	3000 K	80	125 lm/W	995 lm
911401593343	DN589B LED11/840 P8PSD D125 VWB-M G2	4000 K	80	130 lm/W	1,037 lm
911401593643	DN590B LED17/830 P13PSU D125 VWB-M G2	3000 K	80	129 lm/W	1,713 lm
911401593743	DN590B LED17/840 P13PSU D125 VWB-M G2	4000 K	80	134 lm/W	1,786 lm
911401594043	DN590B LED17/830 P14PSD D125 VWB-M G2	3000 K	80	124 lm/W	1,713 lm
911401594143	DN590B LED17/840 P14PSD D125 VWB-M G2	4000 K	80	130 lm/W	1,786 lm
911401594443	DN591B LED22/830 P17PSU D125 VWB-M G2	3000 K	80	128 lm/W	2,181 lm
911401594543	DN591B LED22/840 P17PSU D125 VWB-M G2	4000 K	80	133 lm/W	2,273 lm
911401594843	DN591B LED22/830 P18PSD D125 VWB-M G2	3000 K	80	123 lm/W	2,181 lm
911401594943	DN591B LED22/840 P18PSD D125 VWB-M G2	4000 K	80	129 lm/W	2,273 lm
911401595243	DN591X LED22/840 P17WIA D125 VWB-M G2	4000 K	80	133 lm/W	2,273 lm
911401595443	DN592B LED26/830 P21PSU D125 VWB-M G2	3000 K	80	123 lm/W	2,594 lm
911401595543	DN592B LED26/840 P21PSU D125 VWB-M G2	4000 K	80	128 lm/W	2,703 lm
911401595843	DN592B LED26/830 P22PSD D125 VWB-M G2	3000 K	80	118 lm/W	2,594 lm
911401595943	DN592B LED26/840 P22PSD D125 VWB-M G2	4000 K	80	123 lm/W	2,703 lm
911401596243	DN592X LED26/840 P21WIA D125 VWB-M G2	4000 K	80	128 lm/W	2,703 lm
911401502644	DN590B LED17/840 P10PSU D150 WB UE G2	4000 K	80	167 lm/W	1,661 lm
911401503144	DN591B LED23/840 P17PSU D150 WB WP G2	4000 K	80	134 lm/W	2,261 lm
911401503244	DN592B LED27/830 P21PSU D150 WB G2	3000 K	80	125 lm/W	2,607 lm
911401503344	DN592B LED27/840 P21PSU D150 WB G2	4000 K	80	131 lm/W	2,717 lm
911401596443	DN589B LED12/830 P8PSU D150 WB G2	3000 K	80	135 lm/W	1,110 lm
911401596543	DN589B LED12/840 P8PSU D150 WB G2	4000 K	80	141 lm/W	1,157 lm
911401596643	DN590B LED18/830 P13PSU D150 WB G2	3000 K	80	131 lm/W	1,713 lm
911401596743	DN590B LED18/840 P13PSU D150 WB G2	4000 K	80	136 lm/W	1,786 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401596843	DN591B LED23/830 P17PSU D150 WB G2	3000 K	80	129 lm/W	2,169 lm
911401596943	DN591B LED23/840 P17PSU D150 WB G2	4000 K	80	134 lm/W	2,261 lm
911401597043	DN589B LED12/830 P8PSD D150 WB G2	3000 K	80	126 lm/W	995 lm
911401597143	DN589B LED12/840 P8PSD D150 WB G2	4000 K	80	131 lm/W	1,037 lm
911401597243	DN590B LED18/830 P14PSD D150 WB G2	3000 K	80	126 lm/W	1,713 lm
911401597343	DN590B LED18/840 P14PSD D150 WB G2	4000 K	80	132 lm/W	1,786 lm
911401597443	DN591B LED23/830 P17PSD D150 WB G2	3000 K	80	125 lm/W	2,169 lm
911401597543	DN591B LED23/840 P17PSD D150 WB G2	4000 K	80	130 lm/W	2,261 lm
911401597643	DN589X LED12/840 P9WIA D150 WB G2	4000 K	80	134 lm/W	1,157 lm
911401597743	DN592B LED27/830 P22PSD D150 WB G2	3000 K	80	121 lm/W	2,607 lm
911401597843	DN592B LED27/840 P22PSD D150 WB G2	4000 K	80	126 lm/W	2,717 lm
911401597943	DN592X LED27/840 P21WIA D150 WB G2	4000 K	80	131 lm/W	2,717 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
911401502944	DN589B LED10/840 P8PSU D100 WB WP G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401592243	DN589X LED10/940 P9WIA D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591243	DN588B LED5/930 P4PSU D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401592343	DN590X LED16/940 P14WIA D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591343	DN588B LED5/940 P4PSU D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401500044	DN596B LED80/830 P62PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591443	DN589B LED10/930 P8PSU D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401500144	DN596B LED80/840 P62PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591543	DN589B LED10/940 P8PSU D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401500444	DN596B LED80/830 P59PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591643	DN590B LED16/930 P13PSU D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401500544	DN596B LED80/840 P59PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591743	DN590B LED16/940 P13PSU D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401500844	DN591B LED19/830 P13PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591843	DN589B LED10/930 P8PSD D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401500944	DN591B LED19/840 P13PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401591943	DN589B LED10/940 P8PSD D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401501244	DN591B LED19/830 P13PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401592043	DN590B LED16/930 P14PSD D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401501344	DN591B LED19/840 P13PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401592143	DN590B LED16/940 P14PSD D100 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees	911401501544	DN591X LED19/840 P13WIA D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees

Order Code	Full Product Name	Optic type
911401501844	DN593B LED29/830 P20PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401501944	DN593B LED29/840 P20PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401502244	DN593B LED29/830 P21PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401502344	DN593B LED29/840 P21PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401502844	DN591B LED23/840 P13PSU D200 WB UE G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401598243	DN594B LED42/830 P30PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401598343	DN594B LED42/840 P30PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401598643	DN594B LED42/830 P31PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401598743	DN594B LED42/840 P31PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401598943	DN594X LED42/840 P30WIA D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401599343	DN595B LED61/840 P46PSU D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401599643	DN595B LED61/830 P47PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401599743	DN595B LED61/840 P47PSD D200 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401500244	DN596B LED80/830 P59PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401500344	DN596B LED80/840 P59PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401500644	DN591B LED19/830 P13PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401500744	DN591B LED19/840 P13PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401501044	DN591B LED19/830 P13PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401501144	DN591B LED19/840 P13PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401501444	DN591X LED19/840 P13WIA D200 VWB-M G2	High-efficiency reflector medium beam
911401501644	DN593B LED29/830 P20PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401501744	DN593B LED29/840 P20PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401502044	DN593B LED29/830 P21PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401502144	DN593B LED29/840 P21PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401502744	DN591B LED23/840 P13PSU D200 VWB-M UE G2	High-efficiency reflector medium beam
911401598043	DN594B LED42/830 P30PSU D200 VWB-M G2	High-efficiency reflector medium beam

Order Code	Full Product Name	Optic type
911401598143	DN594B LED42/840 P30PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401598443	DN594B LED42/830 P31PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401598543	DN594B LED42/840 P31PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401598843	DN594X LED42/840 P30WIA D200 VWB-M G2	High-efficiency reflector medium beam
911401599043	DN595B LED61/830 P46PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401599443	DN595B LED61/830 P47PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401599543	DN595B LED61/840 P47PSD D200 VWB-M G2	High-efficiency reflector medium beam
911401599843	DN596B LED80/830 P62PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401599943	DN596B LED80/840 P62PSU D200 VWB-M G2	High-efficiency reflector medium beam
911401502544	DN589B LED12/840 P7PSU D125 WB UE G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401503044	DN590B LED17/840 P13PSU D125 WB WP G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401592643	DN588B LED9/830 P6PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401592743	DN588B LED9/840 P6PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401593043	DN589B LED11/830 P8PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401593143	DN589B LED11/840 P8PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401593443	DN589B LED11/830 P8PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401593543	DN589B LED11/840 P8PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401593843	DN590B LED17/830 P13PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401593943	DN590B LED17/840 P13PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401594243	DN590B LED17/830 P14PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401594343	DN590B LED17/840 P14PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401594643	DN591B LED22/830 P17PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401594743	DN591B LED22/840 P17PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401595043	DN591B LED22/830 P18PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401595143	DN591B LED22/840 P18PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401595343	DN591X LED22/840 P17WIA D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees

Order Code	Full Product Name	Optic type
911401595643	DN592B LED26/830 P21PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401595743	DN592B LED26/840 P21PSU D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596043	DN592B LED26/830 P22PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596143	DN592B LED26/840 P22PSD D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596343	DN592X LED26/840 P21WIA D125 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401588543	DN588B LED5/930 P4PSU D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401588643	DN588B LED5/940 P4PSU D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401588743	DN588B LED5/930 P4PSU D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401588843	DN588B LED5/940 P4PSU D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401588943	DN588B LED5/930 P4PSU D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401589043	DN588B LED5/940 P4PSU D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401589143	DN589B LED10/930 P8PSU D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401589243	DN589B LED10/940 P8PSU D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401589343	DN589B LED10/930 P8PSU D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401589443	DN589B LED10/940 P8PSU D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401589543	DN589B LED10/930 P8PSU D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401589643	DN589B LED10/940 P8PSU D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401589743	DN590B LED15/930 P14PSU D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401589843	DN590B LED15/940 P14PSU D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401589943	DN590B LED15/930 P14PSU D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401590043	DN590B LED15/940 P14PSU D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401590143	DN590B LED15/930 P14PSU D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401590243	DN590B LED15/940 P14PSU D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401590343	DN590B LED15/930 P14PSD D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401590443	DN590B LED15/940 P14PSD D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401590543	DN590B LED15/930 P14PSD D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees

Order Code	Full Product Name	Optic type
911401590643	DN590B LED15/940 P14PSD D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401590743	DN590B LED15/930 P14PSD D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401590843	DN590B LED15/940 P14PSD D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401590943	DN590X LED15/940 P14WIA D75 NB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401591043	DN590X LED15/940 P14WIA D75 MB G2	High-reflective metal reflector Medium beam 20 to 40 degrees
911401591143	DN590X LED15/940 P14WIA D75 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401502444	DN589B LED12/840 P7PSU D125 VWB-M UE G2	High-efficiency reflector medium beam
911401592443	DN588B LED9/830 P6PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401592543	DN588B LED9/840 P6PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401592843	DN589B LED11/830 P8PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401592943	DN589B LED11/840 P8PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401593243	DN589B LED11/830 P8PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401593343	DN589B LED11/840 P8PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401593643	DN590B LED17/830 P13PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401593743	DN590B LED17/840 P13PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401594043	DN590B LED17/830 P14PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401594143	DN590B LED17/840 P14PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401594443	DN591B LED22/830 P17PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401594543	DN591B LED22/840 P17PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401594843	DN591B LED22/830 P18PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401594943	DN591B LED22/840 P18PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401595243	DN591X LED22/840 P17WIA D125 VWB-M G2	High-efficiency reflector medium beam
911401595443	DN592B LED26/830 P21PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401595543	DN592B LED26/840 P21PSU D125 VWB-M G2	High-efficiency reflector medium beam
911401595843	DN592B LED26/830 P22PSD D125 VWB-M G2	High-efficiency reflector medium beam
911401595943	DN592B LED26/840 P22PSD D125 VWB-M G2	High-efficiency reflector medium beam

Order Code	Full Product Name	Optic type
911401596243	DN592X LED26/840 P21WIA D125 VWB-M G2	High-efficiency reflector medium beam
911401502644	DN590B LED17/840 P10PSU D150 WB UE G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401503144	DN591B LED23/840 P17PSU D150 WB WP G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401503244	DN592B LED27/830 P21PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401503344	DN592B LED27/840 P21PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596443	DN589B LED12/830 P8PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596543	DN589B LED12/840 P8PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596643	DN590B LED18/830 P13PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596743	DN590B LED18/840 P13PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596843	DN591B LED23/830 P17PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401596943	DN591B LED23/840 P17PSU D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees

Order Code	Full Product Name	Optic type
911401597043	DN589B LED12/830 P8PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597143	DN589B LED12/840 P8PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597243	DN590B LED18/830 P14PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597343	DN590B LED18/840 P14PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597443	DN591B LED23/830 P17PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597543	DN591B LED23/840 P17PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597643	DN589X LED12/840 P9WIA D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597743	DN592B LED27/830 P22PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597843	DN592B LED27/840 P22PSD D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees
911401597943	DN592X LED27/840 P21WIA D150 WB G2	High-reflective metal reflector Wide beam 40 to 80 degrees

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401502944	DN589B LED10/840 P8PSU D100 WB WP G2	8.4 W
911401591243	DN588B LED5/930 P4PSU D100 WB G2	4.1 W
911401591343	DN588B LED5/940 P4PSU D100 WB G2	4.1 W
911401591443	DN589B LED10/930 P8PSU D100 WB G2	8.4 W
911401591543	DN589B LED10/940 P8PSU D100 WB G2	8.4 W
911401591643	DN590B LED16/930 P13PSU D100 WB G2	13.5 W
911401591743	DN590B LED16/940 P13PSU D100 WB G2	13.5 W
911401591843	DN589B LED10/930 P8PSD D100 WB G2	8.8 W
911401591943	DN589B LED10/940 P8PSD D100 WB G2	8.8 W
911401592043	DN590B LED16/930 P14PSD D100 WB G2	14 W
911401592143	DN590B LED16/940 P14PSD D100 WB G2	14 W
911401592243	DN589X LED10/940 P9WIA D100 WB G2	8.8 W
911401592343	DN590X LED16/940 P14WIA D100 WB G2	13.6 W
911401500044	DN596B LED80/830 P62PSU D200 WB G2	61.6 W
911401500144	DN596B LED80/840 P62PSU D200 WB G2	61.6 W
911401500444	DN596B LED80/830 P59PSD D200 WB G2	59.1 W
911401500544	DN596B LED80/840 P59PSD D200 WB G2	59.1 W
911401500844	DN591B LED19/830 P13PSU D200 WB G2	12.8 W
911401500944	DN591B LED19/840 P13PSU D200 WB G2	12.8 W
911401501244	DN591B LED19/830 P13PSD D200 WB G2	13.3 W
911401501344	DN591B LED19/840 P13PSD D200 WB G2	13.3 W
911401501544	DN591X LED19/840 P13WIA D200 WB G2	12.9 W
911401501844	DN593B LED29/830 P20PSU D200 WB G2	20.1 W
911401501944	DN593B LED29/840 P20PSU D200 WB G2	20.1 W
911401502244	DN593B LED29/830 P21PSD D200 WB G2	20.8 W
911401502344	DN593B LED29/840 P21PSD D200 WB G2	20.8 W

Order Code	Full Product Name	Power Consumption
911401502844	DN591B LED23/840 P13PSU D200 WB UE G2	13.2 W
911401598243	DN594B LED42/830 P30PSU D200 WB G2	29.7 W
911401598343	DN594B LED42/840 P30PSU D200 WB G2	29.7 W
911401598643	DN594B LED42/830 P31PSD D200 WB G2	30.7 W
911401598743	DN594B LED42/840 P31PSD D200 WB G2	30.7 W
911401598943	DN594X LED42/840 P30WIA D200 WB G2	29.7 W
911401599343	DN595B LED61/840 P46PSU D200 WB G2	45.5 W
911401599643	DN595B LED61/830 P47PSD D200 WB G2	46.6 W
911401599743	DN595B LED61/840 P47PSD D200 WB G2	46.6 W
911401500244	DN596B LED80/830 P59PSD D200 VWB-M G2	59.1 W
911401500344	DN596B LED80/840 P59PSD D200 VWB-M G2	59.1 W
911401500644	DN591B LED19/830 P13PSU D200 VWB-M G2	12.8 W
911401500744	DN591B LED19/840 P13PSU D200 VWB-M G2	12.8 W
911401501044	DN591B LED19/830 P13PSD D200 VWB-M G2	13.3 W
911401501144	DN591B LED19/840 P13PSD D200 VWB-M G2	13.3 W
911401501444	DN591X LED19/840 P13WIA D200 VWB-M G2	12.9 W
911401501644	DN593B LED29/830 P20PSU D200 VWB-M G2	20.1 W
911401501744	DN593B LED29/840 P20PSU D200 VWB-M G2	20.1 W
911401502044	DN593B LED29/830 P21PSD D200 VWB-M G2	20.8 W
911401502144	DN593B LED29/840 P21PSD D200 VWB-M G2	20.8 W
911401502744	DN591B LED23/840 P13PSU D200 VWB-M UE G2	13.2 W
911401598043	DN594B LED42/830 P30PSU D200 VWB-M G2	29.7 W
911401598143	DN594B LED42/840 P30PSU D200 VWB-M G2	29.7 W
911401598443	DN594B LED42/830 P31PSD D200 VWB-M G2	30.7 W
911401598543	DN594B LED42/840 P31PSD D200 VWB-M G2	30.7 W
911401598843	DN594X LED42/840 P30WIA D200 VWB-M G2	29.7 W

Order Code	Full Product Name	Power Consumption
911401599043	DN595B LED61/830 P46PSU D200 VWB-M G2	45.5 W
911401599443	DN595B LED61/830 P47PSD D200 VWB-M G2	46.6 W
911401599543	DN595B LED61/840 P47PSD D200 VWB-M G2	46.6 W
911401599843	DN596B LED80/830 P62PSU D200 VWB-M G2	61.6 W
911401599943	DN596B LED80/840 P62PSU D200 VWB-M G2	61.6 W
911401502544	DN589B LED12/840 P7PSU D125 WB UE G2	7.5 W
911401503044	DN590B LED17/840 P13PSU D125 WB WP G2	13.3 W
911401592643	DN588B LED9/830 P6PSU D125 WB G2	6.5 W
911401592743	DN588B LED9/840 P6PSU D125 WB G2	6.5 W
911401593043	DN589B LED11/830 P8PSU D125 WB G2	8.3 W
911401593143	DN589B LED11/840 P8PSU D125 WB G2	8.3 W
911401593443	DN589B LED11/830 P8PSD D125 WB G2	8 W
911401593543	DN589B LED11/840 P8PSD D125 WB G2	8 W
911401593843	DN590B LED17/830 P13PSU D125 WB G2	13.3 W
911401593943	DN590B LED17/840 P13PSU D125 WB G2	13.3 W
911401594243	DN590B LED17/830 P14PSD D125 WB G2	13.8 W
911401594343	DN590B LED17/840 P14PSD D125 WB G2	13.8 W
911401594643	DN591B LED22/830 P17PSU D125 WB G2	16.8 W
911401594743	DN591B LED22/840 P17PSU D125 WB G2	16.8 W
911401595043	DN591B LED22/830 P18PSD D125 WB G2	17.7 W
911401595143	DN591B LED22/840 P18PSD D125 WB G2	17.7 W
911401595343	DN591X LED22/840 P17WIA D125 WB G2	17.1 W
911401595643	DN592B LED26/830 P21PSU D125 WB G2	21.2 W
911401595743	DN592B LED26/840 P21PSU D125 WB G2	21.2 W
911401596043	DN592B LED26/830 P22PSD D125 WB G2	21.9 W
911401596143	DN592B LED26/840 P22PSD D125 WB G2	21.9 W
911401596343	DN592X LED26/840 P21WIA D125 WB G2	21.2 W
911401588543	DN588B LED5/930 P4PSU D75 NB G2	4.2 W
911401588643	DN588B LED5/940 P4PSU D75 NB G2	4.2 W
911401588743	DN588B LED5/930 P4PSU D75 MB G2	4.2 W
911401588843	DN588B LED5/940 P4PSU D75 MB G2	4.2 W
911401588943	DN588B LED5/930 P4PSU D75 WB G2	4.2 W
911401589043	DN588B LED5/940 P4PSU D75 WB G2	4.2 W
911401589143	DN589B LED10/930 P8PSU D75 NB G2	8.5 W
911401589243	DN589B LED10/940 P8PSU D75 NB G2	8.5 W
911401589343	DN589B LED10/930 P8PSU D75 MB G2	8.5 W
911401589443	DN589B LED10/940 P8PSU D75 MB G2	8.5 W
911401589543	DN589B LED10/930 P8PSU D75 WB G2	8.5 W
911401589643	DN589B LED10/940 P8PSU D75 WB G2	8.5 W
911401589743	DN590B LED15/930 P14PSU D75 NB G2	13.6 W
911401589843	DN590B LED15/940 P14PSU D75 NB G2	13.6 W
911401589943	DN590B LED15/930 P14PSU D75 MB G2	13.6 W
911401590043	DN590B LED15/940 P14PSU D75 MB G2	13.6 W
911401590143	DN590B LED15/930 P14PSU D75 WB G2	13.6 W
911401590243	DN590B LED15/940 P14PSU D75 WB G2	13.6 W
911401590343	DN590B LED15/930 P14PSD D75 NB G2	14.1 W
911401590443	DN590B LED15/940 P14PSD D75 NB G2	14.1 W
911401590543	DN590B LED15/930 P14PSD D75 MB G2	14.1 W

Order Code	Full Product Name	Power Consumption
911401590643	DN590B LED15/940 P14PSD D75 MB G2	14.1 W
911401590743	DN590B LED15/930 P14PSD D75 WB G2	14.1 W
911401590843	DN590B LED15/940 P14PSD D75 WB G2	14.1 W
911401590943	DN590X LED15/940 P14WIA D75 NB G2	13.8 W
911401591043	DN590X LED15/940 P14WIA D75 MB G2	13.8 W
911401591143	DN590X LED15/940 P14WIA D75 WB G2	13.8 W
911401502444	DN589B LED12/840 P7PSU D125 VWB-M UE G2	7.5 W
911401592443	DN588B LED9/830 P6PSU D125 VWB-M G2	6.5 W
911401592543	DN588B LED9/840 P6PSU D125 VWB-M G2	6.5 W
911401592843	DN589B LED11/830 P8PSU D125 VWB-M G2	8.3 W
911401592943	DN589B LED11/840 P8PSU D125 VWB-M G2	8.3 W
911401593243	DN589B LED11/830 P8PSD D125 VWB-M G2	8 W
911401593343	DN589B LED11/840 P8PSD D125 VWB-M G2	8 W
911401593643	DN590B LED17/830 P13PSU D125 VWB-M G2	13.3 W
911401593743	DN590B LED17/840 P13PSU D125 VWB-M G2	13.3 W
911401594043	DN590B LED17/830 P14PSD D125 VWB-M G2	13.8 W
911401594143	DN590B LED17/840 P14PSD D125 VWB-M G2	13.8 W
911401594443	DN591B LED22/830 P17PSU D125 VWB-M G2	16.8 W
911401594543	DN591B LED22/840 P17PSU D125 VWB-M G2	16.8 W
911401594843	DN591B LED22/830 P18PSD D125 VWB-M G2	17.7 W
911401594943	DN591B LED22/840 P18PSD D125 VWB-M G2	17.7 W
911401595243	DN591X LED22/840 P17WIA D125 VWB-M G2	17.1 W
911401595443	DN592B LED26/830 P21PSU D125 VWB-M G2	21.2 W
911401595543	DN592B LED26/840 P21PSU D125 VWB-M G2	21.2 W
911401595843	DN592B LED26/830 P22PSD D125 VWB-M G2	21.9 W
911401595943	DN592B LED26/840 P22PSD D125 VWB-M G2	21.9 W
911401596243	DN592X LED26/840 P21WIA D125 VWB-M G2	21.2 W
911401502644	DN590B LED17/840 P10PSU D150 WB UE G2	10 W
911401503144	DN591B LED23/840 P17PSU D150 WB WP G2	16.8 W
911401503244	DN592B LED27/830 P21PSU D150 WB G2	20.8 W
911401503344	DN592B LED27/840 P21PSU D150 WB G2	20.8 W
911401596443	DN589B LED12/830 P8PSU D150 WB G2	8.2 W
911401596543	DN589B LED12/840 P8PSU D150 WB G2	8.2 W
911401596643	DN590B LED18/830 P13PSU D150 WB G2	13.1 W
911401596743	DN590B LED18/840 P13PSU D150 WB G2	13.1 W
911401596843	DN591B LED23/830 P17PSU D150 WB G2	16.8 W
911401596943	DN591B LED23/840 P17PSU D150 WB G2	16.8 W
911401597043	DN589B LED12/830 P8PSD D150 WB G2	7.9 W
911401597143	DN589B LED12/840 P8PSD D150 WB G2	7.9 W
911401597243	DN590B LED18/830 P14PSD D150 WB G2	13.6 W
911401597343	DN590B LED18/840 P14PSD D150 WB G2	13.6 W
911401597443	DN591B LED23/830 P17PSD D150 WB G2	17.4 W
911401597543	DN591B LED23/840 P17PSD D150 WB G2	17.4 W
911401597643	DN589X LED12/840 P9WIA D150 WB G2	8.6 W
911401597743	DN592B LED27/830 P22PSD D150 WB G2	21.5 W
911401597843	DN592B LED27/840 P22PSD D150 WB G2	21.5 W
911401597943	DN592X LED27/840 P21WIA D150 WB G2	20.8 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401502944	DN589B LED10/840 P8PSU D100 WB WP G2	No	-
911401591243	DN588B LED5/930 P4PSU D100 WB G2	No	-
911401591343	DN588B LED5/940 P4PSU D100 WB G2	No	-
911401591443	DN589B LED10/930 P8PSU D100 WB G2	No	-
911401591543	DN589B LED10/940 P8PSU D100 WB G2	No	-
911401591643	DN590B LED16/930 P13PSU D100 WB G2	No	-
911401591743	DN590B LED16/940 P13PSU D100 WB G2	No	-
911401591843	DN589B LED10/930 P8PSD D100 WB G2	Yes	1%
911401591943	DN589B LED10/940 P8PSD D100 WB G2	Yes	1%
911401592043	DN590B LED16/930 P14PSD D100 WB G2	Yes	1%
911401592143	DN590B LED16/940 P14PSD D100 WB G2	Yes	1%
911401592243	DN589X LED10/940 P9WIA D100 WB G2	Yes	3%
911401592343	DN590X LED16/940 P14WIA D100 WB G2	Yes	1%
911401500044	DN596B LED80/830 P62PSU D200 WB G2	No	-
911401500144	DN596B LED80/840 P62PSU D200 WB G2	No	-
911401500444	DN596B LED80/830 P59PSD D200 WB G2	Yes	1%
911401500544	DN596B LED80/840 P59PSD D200 WB G2	Yes	1%
911401500844	DN591B LED19/830 P13PSU D200 WB G2	No	-
911401500944	DN591B LED19/840 P13PSU D200 WB G2	No	-
911401501244	DN591B LED19/830 P13PSD D200 WB G2	Yes	1%
911401501344	DN591B LED19/840 P13PSD D200 WB G2	Yes	1%
911401501544	DN591X LED19/840 P13WIA D200 WB G2	Yes	1%
911401501844	DN593B LED29/830 P20PSU D200 WB G2	No	-
911401501944	DN593B LED29/840 P20PSU D200 WB G2	No	-
911401502244	DN593B LED29/830 P21PSD D200 WB G2	Yes	1%
911401502344	DN593B LED29/840 P21PSD D200 WB G2	Yes	1%
911401502844	DN591B LED23/840 P13PSU D200 WB UE G2	No	-
911401598243	DN594B LED42/830 P30PSU D200 WB G2	No	-
911401598343	DN594B LED42/840 P30PSU D200 WB G2	No	-
911401598643	DN594B LED42/830 P31PSD D200 WB G2	Yes	1%
911401598743	DN594B LED42/840 P31PSD D200 WB G2	Yes	1%
911401598943	DN594X LED42/840 P30WIA D200 WB G2	Yes	1%
911401599343	DN595B LED61/840 P46PSU D200 WB G2	No	-
911401599643	DN595B LED61/830 P47PSD D200 WB G2	Yes	1%
911401599743	DN595B LED61/840 P47PSD D200 WB G2	Yes	1%
911401500244	DN596B LED80/830 P59PSD D200 VWB-M G2	Yes	1%
911401500344	DN596B LED80/840 P59PSD D200 VWB-M G2	Yes	1%
911401500644	DN591B LED19/830 P13PSU D200 VWB-M G2	No	-
911401500744	DN591B LED19/840 P13PSU D200 VWB-M G2	No	-
911401501044	DN591B LED19/830 P13PSD D200 VWB-M G2	Yes	1%
911401501144	DN591B LED19/840 P13PSD D200 VWB-M G2	Yes	1%
911401501444	DN591X LED19/840 P13WIA D200 VWB-M G2	Yes	1%

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401501644	DN593B LED29/830 P20PSU D200 VWB-M G2	No	-
911401501744	DN593B LED29/840 P20PSU D200 VWB-M G2	No	-
911401502044	DN593B LED29/830 P21PSD D200 VWB-M G2	Yes	1%
911401502144	DN593B LED29/840 P21PSD D200 VWB-M G2	Yes	1%
911401502744	DN591B LED23/840 P13PSU D200 VWB-M UE G2	No	-
911401598043	DN594B LED42/830 P30PSU D200 VWB-M G2	No	-
911401598143	DN594B LED42/840 P30PSU D200 VWB-M G2	No	-
911401598443	DN594B LED42/830 P31PSD D200 VWB-M G2	Yes	1%
911401598543	DN594B LED42/840 P31PSD D200 VWB-M G2	Yes	1%
911401598843	DN594X LED42/840 P30WIA D200 VWB-M G2	Yes	1%
911401599043	DN595B LED61/830 P46PSU D200 VWB-M G2	No	-
911401599443	DN595B LED61/830 P47PSD D200 VWB-M G2	Yes	1%
911401599543	DN595B LED61/840 P47PSD D200 VWB-M G2	Yes	1%
911401599843	DN596B LED80/830 P62PSU D200 VWB-M G2	No	-
911401599943	DN596B LED80/840 P62PSU D200 VWB-M G2	No	-
911401502544	DN589B LED12/840 P7PSU D125 WB UE G2	No	-
911401503044	DN590B LED17/840 P13PSU D125 WB WP G2	No	-
911401592643	DN588B LED9/830 P6PSU D125 WB G2	No	-
911401592743	DN588B LED9/840 P6PSU D125 WB G2	No	-
911401593043	DN589B LED11/830 P8PSU D125 WB G2	No	-
911401593143	DN589B LED11/840 P8PSU D125 WB G2	No	-
911401593443	DN589B LED11/830 P8PSD D125 WB G2	Yes	1%
911401593543	DN589B LED11/840 P8PSD D125 WB G2	Yes	1%
911401593843	DN590B LED17/830 P13PSU D125 WB G2	No	-
911401593943	DN590B LED17/840 P13PSU D125 WB G2	No	-
911401594243	DN590B LED17/830 P14PSD D125 WB G2	Yes	1%
911401594343	DN590B LED17/840 P14PSD D125 WB G2	Yes	1%
911401594643	DN591B LED22/830 P17PSU D125 WB G2	No	-
911401594743	DN591B LED22/840 P17PSU D125 WB G2	No	-
911401595043	DN591B LED22/830 P18PSD D125 WB G2	Yes	1%
911401595143	DN591B LED22/840 P18PSD D125 WB G2	Yes	1%
911401595343	DN591X LED22/840 P17WIA D125 WB G2	Yes	1%
911401595643	DN592B LED26/830 P21PSU D125 WB G2	No	-
911401595743	DN592B LED26/840 P21PSU D125 WB G2	No	-
911401596043	DN592B LED26/830 P22PSD D125 WB G2	Yes	1%

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401596143	DN592B LED26/840 P22PSD D125 WB G2	Yes	1%
911401596343	DN592X LED26/840 P21WIA D125 WB G2	Yes	1%
911401588543	DN588B LED5/930 P4PSU D75 NB G2	No	-
911401588643	DN588B LED5/940 P4PSU D75 NB G2	No	-
911401588743	DN588B LED5/930 P4PSU D75 MB G2	No	-
911401588843	DN588B LED5/940 P4PSU D75 MB G2	No	-
911401588943	DN588B LED5/930 P4PSU D75 WB G2	No	-
911401589043	DN588B LED5/940 P4PSU D75 WB G2	No	-
911401589143	DN589B LED10/930 P8PSU D75 NB G2	No	-
911401589243	DN589B LED10/940 P8PSU D75 NB G2	No	-
911401589343	DN589B LED10/930 P8PSU D75 MB G2	No	-
911401589443	DN589B LED10/940 P8PSU D75 MB G2	No	-
911401589543	DN589B LED10/930 P8PSU D75 WB G2	No	-
911401589643	DN589B LED10/940 P8PSU D75 WB G2	No	-
911401589743	DN590B LED15/930 P14PSU D75 NB G2	No	-
911401589843	DN590B LED15/940 P14PSU D75 NB G2	No	-
911401589943	DN590B LED15/930 P14PSU D75 MB G2	No	-
911401590043	DN590B LED15/940 P14PSU D75 MB G2	No	-
911401590143	DN590B LED15/930 P14PSU D75 WB G2	No	-
911401590243	DN590B LED15/940 P14PSU D75 WB G2	No	-
911401590343	DN590B LED15/930 P14PSD D75 NB G2	Yes	1%
911401590443	DN590B LED15/940 P14PSD D75 NB G2	Yes	1%
911401590543	DN590B LED15/930 P14PSD D75 MB G2	Yes	1%
911401590643	DN590B LED15/940 P14PSD D75 MB G2	Yes	1%
911401590743	DN590B LED15/930 P14PSD D75 WB G2	Yes	1%
911401590843	DN590B LED15/940 P14PSD D75 WB G2	Yes	1%
911401590943	DN590X LED15/940 P14WIA D75 NB G2	Yes	1%
911401591043	DN590X LED15/940 P14WIA D75 MB G2	Yes	1%
911401591143	DN590X LED15/940 P14WIA D75 WB G2	Yes	1%
911401502444	DN589B LED12/840 P7PSU D125 VWB-M UE G2	No	-
911401592443	DN588B LED9/830 P6PSU D125 VWB-M G2	No	-
911401592543	DN588B LED9/840 P6PSU D125 VWB-M G2	No	-
911401592843	DN589B LED11/830 P8PSU D125 VWB-M G2	No	-
911401592943	DN589B LED11/840 P8PSU D125 VWB-M G2	No	-
911401593243	DN589B LED11/830 P8PSD D125 VWB-M G2	Yes	1%
911401593343	DN589B LED11/840 P8PSD D125 VWB-M G2	Yes	1%
911401593643	DN590B LED17/830 P13PSU D125 VWB-M G2	No	-
911401593743	DN590B LED17/840 P13PSU D125 VWB-M G2	No	-

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401594043	DN590B LED17/830 P14PSD D125 VWB-M G2	Yes	1%
911401594143	DN590B LED17/840 P14PSD D125 VWB-M G2	Yes	1%
911401594443	DN591B LED22/830 P17PSU D125 VWB-M G2	No	-
911401594543	DN591B LED22/840 P17PSU D125 VWB-M G2	No	-
911401594843	DN591B LED22/830 P18PSD D125 VWB-M G2	Yes	1%
911401594943	DN591B LED22/840 P18PSD D125 VWB-M G2	Yes	1%
911401595243	DN591X LED22/840 P17WIA D125 VWB-M G2	Yes	1%
911401595443	DN592B LED26/830 P21PSU D125 VWB-M G2	No	-
911401595543	DN592B LED26/840 P21PSU D125 VWB-M G2	No	-
911401595843	DN592B LED26/830 P22PSD D125 VWB-M G2	Yes	1%
911401595943	DN592B LED26/840 P22PSD D125 VWB-M G2	Yes	1%
911401596243	DN592X LED26/840 P21WIA D125 VWB-M G2	Yes	1%
911401502644	DN590B LED17/840 P10PSU D150 WB UE G2	No	-
911401503144	DN591B LED23/840 P17PSU D150 WB WP G2	No	-
911401503244	DN592B LED27/830 P21PSU D150 WB G2	No	-
911401503344	DN592B LED27/840 P21PSU D150 WB G2	No	-
911401596443	DN589B LED12/830 P8PSU D150 WB G2	No	-
911401596543	DN589B LED12/840 P8PSU D150 WB G2	No	-
911401596643	DN590B LED18/830 P13PSU D150 WB G2	No	-
911401596743	DN590B LED18/840 P13PSU D150 WB G2	No	-
911401596843	DN591B LED23/830 P17PSU D150 WB G2	No	-
911401596943	DN591B LED23/840 P17PSU D150 WB G2	No	-
911401597043	DN589B LED12/830 P8PSD D150 WB G2	Yes	1%
911401597143	DN589B LED12/840 P8PSD D150 WB G2	Yes	1%
911401597243	DN590B LED18/830 P14PSD D150 WB G2	Yes	1%
911401597343	DN590B LED18/840 P14PSD D150 WB G2	Yes	1%
911401597443	DN591B LED23/830 P17PSD D150 WB G2	Yes	1%
911401597543	DN591B LED23/840 P17PSD D150 WB G2	Yes	1%
911401597643	DN589X LED12/840 P9WIA D150 WB G2	Yes	3%
911401597743	DN592B LED27/830 P22PSD D150 WB G2	Yes	1%
911401597843	DN592B LED27/840 P22PSD D150 WB G2	Yes	1%
911401597943	DN592X LED27/840 P21WIA D150 WB G2	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
911401502944	DN589B LED10/840 P8PSU D100 WB WP G2	IP20/65
911401591243	DN588B LED5/930 P4PSU D100 WB G2	IP20
911401591343	DN588B LED5/940 P4PSU D100 WB G2	IP20
911401591443	DN589B LED10/930 P8PSU D100 WB G2	IP20
911401591543	DN589B LED10/940 P8PSU D100 WB G2	IP20
911401591643	DN590B LED16/930 P13PSU D100 WB G2	IP20
911401591743	DN590B LED16/940 P13PSU D100 WB G2	IP20
911401591843	DN589B LED10/930 P8PSD D100 WB G2	IP20
911401591943	DN589B LED10/940 P8PSD D100 WB G2	IP20
911401592043	DN590B LED16/930 P14PSD D100 WB G2	IP20
911401592143	DN590B LED16/940 P14PSD D100 WB G2	IP20
911401592243	DN589X LED10/940 P9WIA D100 WB G2	IP20
911401592343	DN590X LED16/940 P14WIA D100 WB G2	IP20
911401500044	DN596B LED80/830 P62PSU D200 WB G2	IP20
911401500144	DN596B LED80/840 P62PSU D200 WB G2	IP20
911401500444	DN596B LED80/830 P59PSD D200 WB G2	IP20
911401500544	DN596B LED80/840 P59PSD D200 WB G2	IP20
911401500844	DN591B LED19/830 P13PSU D200 WB G2	IP20
911401500944	DN591B LED19/840 P13PSU D200 WB G2	IP20
911401501244	DN591B LED19/830 P13PSD D200 WB G2	IP20
911401501344	DN591B LED19/840 P13PSD D200 WB G2	IP20
911401501544	DN591X LED19/840 P13WIA D200 WB G2	IP20
911401501844	DN593B LED29/830 P20PSU D200 WB G2	IP20
911401501944	DN593B LED29/840 P20PSU D200 WB G2	IP20
911401502244	DN593B LED29/830 P21PSD D200 WB G2	IP20
911401502344	DN593B LED29/840 P21PSD D200 WB G2	IP20
911401502844	DN591B LED23/840 P13PSU D200 WB UE G2	IP20
911401598243	DN594B LED42/830 P30PSU D200 WB G2	IP20
911401598343	DN594B LED42/840 P30PSU D200 WB G2	IP20
911401598643	DN594B LED42/830 P31PSD D200 WB G2	IP20
911401598743	DN594B LED42/840 P31PSD D200 WB G2	IP20
911401598943	DN594X LED42/840 P30WIA D200 WB G2	IP20
911401599343	DN595B LED61/840 P46PSU D200 WB G2	IP20
911401599643	DN595B LED61/830 P47PSD D200 WB G2	IP20
911401599743	DN595B LED61/840 P47PSD D200 WB G2	IP20
911401500244	DN596B LED80/830 P59PSD D200 VWB-M G2	IP20
911401500344	DN596B LED80/840 P59PSD D200 VWB-M G2	IP20
911401500644	DN591B LED19/830 P13PSU D200 VWB-M G2	IP20
911401500744	DN591B LED19/840 P13PSU D200 VWB-M G2	IP20
911401501044	DN591B LED19/830 P13PSD D200 VWB-M G2	IP20
911401501144	DN591B LED19/840 P13PSD D200 VWB-M G2	IP20
911401501444	DN591X LED19/840 P13WIA D200 VWB-M G2	IP20
911401501644	DN593B LED29/830 P20PSU D200 VWB-M G2	IP20
911401501744	DN593B LED29/840 P20PSU D200 VWB-M G2	IP20
911401502044	DN593B LED29/830 P21PSD D200 VWB-M G2	IP20
911401502144	DN593B LED29/840 P21PSD D200 VWB-M G2	IP20
911401502744	DN591B LED23/840 P13PSU D200 VWB-M UE G2	IP20
911401598043	DN594B LED42/830 P30PSU D200 VWB-M G2	IP20
911401598143	DN594B LED42/840 P30PSU D200 VWB-M G2	IP20
911401598443	DN594B LED42/830 P31PSD D200 VWB-M G2	IP20
911401598543	DN594B LED42/840 P31PSD D200 VWB-M G2	IP20

Order Code	Full Product Name	Ingress protection code
911401598843	DN594X LED42/840 P30WIA D200 VWB-M G2	IP20
911401599043	DN595B LED61/830 P46PSU D200 VWB-M G2	IP20
911401599443	DN595B LED61/830 P47PSD D200 VWB-M G2	IP20
911401599543	DN595B LED61/840 P47PSD D200 VWB-M G2	IP20
911401599843	DN596B LED80/830 P62PSU D200 VWB-M G2	IP20
911401599943	DN596B LED80/840 P62PSU D200 VWB-M G2	IP20
911401502544	DN589B LED12/840 P7PSU D125 WB UE G2	IP20
911401503044	DN590B LED17/840 P13PSU D125 WB WP G2	IP20/65
911401592643	DN588B LED9/830 P6PSU D125 WB G2	IP20
911401592743	DN588B LED9/840 P6PSU D125 WB G2	IP20
911401593043	DN589B LED11/830 P8PSU D125 WB G2	IP20
911401593143	DN589B LED11/840 P8PSU D125 WB G2	IP20
911401593443	DN589B LED11/830 P8PSD D125 WB G2	IP20
911401593543	DN589B LED11/840 P8PSD D125 WB G2	IP20
911401593843	DN590B LED17/830 P13PSU D125 WB G2	IP20
911401593943	DN590B LED17/840 P13PSU D125 WB G2	IP20
911401594243	DN590B LED17/830 P14PSD D125 WB G2	IP20
911401594343	DN590B LED17/840 P14PSD D125 WB G2	IP20
911401594643	DN591B LED22/830 P17PSU D125 WB G2	IP20
911401594743	DN591B LED22/840 P17PSU D125 WB G2	IP20
911401595043	DN591B LED22/830 P18PSD D125 WB G2	IP20
911401595143	DN591B LED22/840 P18PSD D125 WB G2	IP20
911401595343	DN591X LED22/840 P17WIA D125 WB G2	IP20
911401595643	DN592B LED26/830 P21PSU D125 WB G2	IP20
911401595743	DN592B LED26/840 P21PSU D125 WB G2	IP20
911401596043	DN592B LED26/830 P22PSD D125 WB G2	IP20
911401596143	DN592B LED26/840 P22PSD D125 WB G2	IP20
911401596343	DN592X LED26/840 P21WIA D125 WB G2	IP20
911401588543	DN588B LED5/930 P4PSU D75 NB G2	IP20
911401588643	DN588B LED5/940 P4PSU D75 NB G2	IP20
911401588743	DN588B LED5/930 P4PSU D75 MB G2	IP20
911401588843	DN588B LED5/940 P4PSU D75 MB G2	IP20
911401588943	DN588B LED5/930 P4PSU D75 WB G2	IP20
911401589043	DN588B LED5/940 P4PSU D75 WB G2	IP20
911401589143	DN589B LED10/930 P8PSU D75 NB G2	IP20
911401589243	DN589B LED10/940 P8PSU D75 NB G2	IP20
911401589343	DN589B LED10/930 P8PSU D75 MB G2	IP20
911401589443	DN589B LED10/940 P8PSU D75 MB G2	IP20
911401589543	DN589B LED10/930 P8PSU D75 WB G2	IP20
911401589643	DN589B LED10/940 P8PSU D75 WB G2	IP20
911401589743	DN590B LED15/930 P14PSU D75 NB G2	IP20
911401589843	DN590B LED15/940 P14PSU D75 NB G2	IP20
911401589943	DN590B LED15/930 P14PSU D75 MB G2	IP20
911401590043	DN590B LED15/940 P14PSU D75 MB G2	IP20
911401590143	DN590B LED15/930 P14PSU D75 WB G2	IP20
911401590243	DN590B LED15/940 P14PSU D75 WB G2	IP20
911401590343	DN590B LED15/930 P14PSD D75 NB G2	IP20
911401590443	DN590B LED15/940 P14PSD D75 NB G2	IP20
911401590543	DN590B LED15/930 P14PSD D75 MB G2	IP20
911401590643	DN590B LED15/940 P14PSD D75 MB G2	IP20
911401590743	DN590B LED15/930 P14PSD D75 WB G2	IP20

Order Code	Full Product Name	Ingress protection code
911401590843	DN590B LED15/940 P14PSD D75 WB G2	IP20
911401590943	DN590X LED15/940 P14WIA D75 NB G2	IP20
911401591043	DN590X LED15/940 P14WIA D75 MB G2	IP20
911401591143	DN590X LED15/940 P14WIA D75 WB G2	IP20
911401502444	DN589B LED12/840 P7PSU D125 VWB-M UE G2	IP20
911401592443	DN588B LED9/830 P6PSU D125 VWB-M G2	IP20
911401592543	DN588B LED9/840 P6PSU D125 VWB-M G2	IP20
911401592843	DN589B LED11/830 P8PSU D125 VWB-M G2	IP20
911401592943	DN589B LED11/840 P8PSU D125 VWB-M G2	IP20
911401593243	DN589B LED11/830 P8PSD D125 VWB-M G2	IP20
911401593343	DN589B LED11/840 P8PSD D125 VWB-M G2	IP20
911401593643	DN590B LED17/830 P13PSU D125 VWB-M G2	IP20
911401593743	DN590B LED17/840 P13PSU D125 VWB-M G2	IP20
911401594043	DN590B LED17/830 P14PSD D125 VWB-M G2	IP20
911401594143	DN590B LED17/840 P14PSD D125 VWB-M G2	IP20
911401594443	DN591B LED22/830 P17PSU D125 VWB-M G2	IP20
911401594543	DN591B LED22/840 P17PSU D125 VWB-M G2	IP20
911401594843	DN591B LED22/830 P18PSD D125 VWB-M G2	IP20
911401594943	DN591B LED22/840 P18PSD D125 VWB-M G2	IP20
911401595243	DN591X LED22/840 P17WIA D125 VWB-M G2	IP20
911401595443	DN592B LED26/830 P21PSU D125 VWB-M G2	IP20
911401595543	DN592B LED26/840 P21PSU D125 VWB-M G2	IP20
911401595843	DN592B LED26/830 P22PSD D125 VWB-M G2	IP20

Order Code	Full Product Name	Ingress protection code
911401595943	DN592B LED26/840 P22PSD D125 VWB-M G2	IP20
911401596243	DN592X LED26/840 P21WIA D125 VWB-M G2	IP20
911401502644	DN590B LED17/840 P10PSU D150 WB UE G2	IP20
911401503144	DN591B LED23/840 P17PSU D150 WB WP G2	IP20/65
911401503244	DN592B LED27/830 P21PSU D150 WB G2	IP20
911401503344	DN592B LED27/840 P21PSU D150 WB G2	IP20
911401596443	DN589B LED12/830 P8PSU D150 WB G2	IP20
911401596543	DN589B LED12/840 P8PSU D150 WB G2	IP20
911401596643	DN590B LED18/830 P13PSU D150 WB G2	IP20
911401596743	DN590B LED18/840 P13PSU D150 WB G2	IP20
911401596843	DN591B LED23/830 P17PSU D150 WB G2	IP20
911401596943	DN591B LED23/840 P17PSU D150 WB G2	IP20
911401597043	DN589B LED12/830 P8PSD D150 WB G2	IP20
911401597143	DN589B LED12/840 P8PSD D150 WB G2	IP20
911401597243	DN590B LED18/830 P14PSD D150 WB G2	IP20
911401597343	DN590B LED18/840 P14PSD D150 WB G2	IP20
911401597443	DN591B LED23/830 P17PSD D150 WB G2	IP20
911401597543	DN591B LED23/840 P17PSD D150 WB G2	IP20
911401597643	DN589X LED12/840 P9WIA D150 WB G2	IP20
911401597743	DN592B LED27/830 P22PSD D150 WB G2	IP20
911401597843	DN592B LED27/840 P22PSD D150 WB G2	IP20
911401597943	DN592X LED27/840 P21WIA D150 WB G2	IP20

