



# High quality and robust performance

## PrimaVision Compact for CDM

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

### Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- CDM lamp life increased by up to 30%
- Eliminates all visible lamp flicker

### Features


- Minimal lamp power spread
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

### Application


- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

PrimaVision Compact for CDM


Versions



GPPR\_IPVG4pp\_PHL\_0001-Product photo







GPPR IPVG4pp PHL 0007



GPPR IPVG4pp PHL 0010

Dimensional drawing




Product	D1	C1	A1	A2	B1
HID-PV C 35 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm
HID-PV C 50 /I CDM 220-240V 50/60Hz	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm
HID-PV C 70 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

Product	D1	C1	A1	A2	B1	B2
HID-PV C 35 /S CDM 220-240V 50/60Hz NG	4.9 mm	32.2 mm	109.6 mm	98.5 mm	74.4 mm	63.7 mm
HID-PV C 50 /S CDM 220-240V 50/60Hz	4.9 mm	32.2 mm	109.6 mm	98.5 mm	74.4 mm	
HID-PV C 70 /S CDM 220-240V 50/60Hz NG	4.9 mm	32.2 mm	109.6 mm	98.5 mm	74.4 mm	63.7 mm

Product	D1	C1	A1	A2	B1	B2
HID-PV C 70 /P CDM 220-240V 50/60Hz	4.9 mm	29.6 mm	106.6 mm	98.5 mm	71.6 mm	63.7 mm

# PrimaVision Compact for CDM

## Product details



HID-PV C 50 /I



HID-PV C 50 /S

### Operating and Electrical

Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

## Operating and Electrical

Order Code	Full Product Name	Number of Products on MCB (16A Type B) (Nom)
913700665166	HID-PV C 50 /I CDM 220-240V 50/60Hz	24
913700653066	HID-PV C 70 /P CDM 220-240V 50/60Hz	20
913700653166	HID-PV C 35 /I CDM 220-240V 50/60Hz NG	24
913700653266	HID-PV C 70 /I CDM 220-240V 50/60Hz NG	20

Order Code	Full Product Name	Number of Products on MCB (16A Type B) (Nom)
913700652766	HID-PV C 35 /S CDM 220-240V 50/60Hz NG	24
913700652966	HID-PV C 70 /S CDM 220-240V 50/60Hz NG	20
913700664966	HID-PV C 50 /S CDM 220-240V 50/60Hz	24

## Mechanical and Housing

Order Code	Full Product Name	Housing
913700665166	HID-PV C 50 /I CDM 220-240V 50/60Hz	/I
913700653066	HID-PV C 70 /P CDM 220-240V 50/60Hz	/P
913700653166	HID-PV C 35 /I CDM 220-240V 50/60Hz NG	/I
913700653266	HID-PV C 70 /I CDM 220-240V 50/60Hz NG	/I

Order Code	Full Product Name	Housing
913700652766	HID-PV C 35 /S CDM 220-240V 50/60Hz NG	/S
913700652966	HID-PV C 70 /S CDM 220-240V 50/60Hz NG	/S
913700664966	HID-PV C 50 /S CDM 220-240V 50/60Hz	/S

