



PrimaVision Power (100W & 150W) for CDM – High power packed in a small size

PrimaVision Power for CDM

PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- Lamp life increased by up to 30% for CDM lamps
- Eliminates all visible lamp flicker

Features

- Loop Through feature (in independent version)
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

Application

- 100 and 150 W: high-bay area, accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

PrimaVision Power for CDM

Versions






GPPR_IPVG4U_0003-Product photo



GPPR_IPVG4U_0006-Product photo

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 150 /I CDM 220-240V 50/60Hz	4.8 mm	34.2 mm	223.9 mm	206.0 mm	82.7 mm

Product	D1	C1	A1	A2	B1	B2
HID-PV C 150 /S CDM 220-240V 50/60Hz	4.8 mm	32.0 mm	135.0 mm	123.5 mm	75.0 mm	63.5 mm



PrimaVision Power for CDM

Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	6

Mechanical and Housing

Order Code	Full Product Name	Housing
913700614066	HID-PV C 150 /S CDM 220-240V 50/60Hz	/S

Order Code	Full Product Name	Housing
913700624466	HID-PV C 150 /I CDM 220-240V 50/60Hz	/I

