



产品描述

MASTER SON-T PIA Plus

高压钠灯，透明外部灯泡，使用寿命长且稳定，输出较高

优点

- 高光效,光效达 150lm/W,更节能
- 超高科技带来可靠长寿命,减少维护费用
- 高流明维持率,保证整个使用过程中的照明效果
- 不含铅,更加环保
- 早期失效率低,确保优秀的一致性
- 可以调光,可以使用调光镇流器进行节能改造

特点

- 使用多晶氧化铝陶瓷放电管,减少使用过程中钠元素的逃逸
- 陶瓷放电管内使用了飞利浦 PIA 一体化天线专利技术,寿命更长,更可靠
- 焊点少且结构结实,抗震动与冲击的能力更强,并进一步减少了早期失效
- 固体消气片,确保了最佳光通维持率,减少了早期失效
- 可以调光
- 不含铅

应用

- 道路照明
- 城市美化照明
- 工业区域照明

安全提示

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER SON-T PIA Plus

Versions




LPPR SON-TPIA Plus E40



LPPR SON-TPIA 0007

二维绘图



Product	D (max)	O	L	C (max)
MASTER SON-T PIA PLUS 150W E E40 1SL/12	47 mm	61 mm	132 mm	209 mm
MST SON-T PIA PLUS 250W E E40 1SL/12	48 mm	64 mm	158 mm	257 mm
MST SON-T PIA PLUS 400W E E40 1SL/12	48 mm	83 mm	175 mm	279 mm
MST SON-T PIA Plus 100W E E40	47 mm	47 mm	132 mm	209 mm
MST SON-T PIA Plus 600W/220 E40 1SL/12	47 mm	126 mm	174.2 mm	279 mm
MST SON-T PIA Plus 70W/220 E27 1SL/12	36 mm	42 mm	104 mm	156 mm

一般信息	
操作位置	UNIVERSAL
灯技术	
显色指数 (CRI)	-
机械和外壳	
灯泡外观	透明

一般信息

Order Code	Full Product Name	底盖
928144709298	MST SON-T PIA PLUS 250W E E40 1SL/12	E40
928144809298	MST SON-T PIA PLUS 400W E E40 1SL/12	E40
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	E40

Order Code	Full Product Name	底盖
928483300094	MST SON-T PIA Plus 100W E E40	E40
928483400093	MASTER SON-T PIA PLUS 150W E E40 1SL/12	E40
928152700028	MST SON-T PIA Plus 70W/220 E27 1SL/12	E27

灯技术

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	相关色温 (标称)	光效 (额定) (标称)	光通量
928144709298	MST SON-T PIA PLUS 250W E E40 1SL/12	0.535	0.420	2000 K	125 lm/W	32,100 lm
928144809298	MST SON-T PIA PLUS 400W E E40 1SL/12	0.535	0.420	2000 K	137 lm/W	-
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	0.530	0.428	2000 K	149 lm/W	-
928483300094	MST SON-T PIA Plus 100W E E40	0.535	0.420	2000 K	105 lm/W	10,600 lm

MASTER SON-T PIA Plus

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	相关色温 (标称)	光效 (额定) (标称)	光通量
928483400093	MASTER SON-T PIA PLUS 150W E E40 1SL/12	0.535	0.420	2000 K	115 lm/W	17,800 lm
928152700028	MST SON-T PIA Plus 70W/220 E27 1SL/12	0.54	0.42	1900 K	90 lm/W	6,650 lm

操作和电气

Order Code	Full Product Name	电压 (标称)	功耗	Order Code	Full Product Name	电压 (标称)	功耗
928144709298	MST SON-T PIA PLUS 250W E E40 1SL/12	102 V	257.0 W	928483300094	MST SON-T PIA Plus 100W E E40	100 V	100.4 W
928144809298	MST SON-T PIA PLUS 400W E E40 1SL/12	105 V	408.0 W	928483400093	MASTER SON-T PIA PLUS 150W E E40 1SL/12	100 V	154.0 W
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	110 V	603 W	928152700028	MST SON-T PIA Plus 70W/220 E27 1SL/12	92 V	74 W

控制和调光

Order Code	Full Product Name	可调光	Order Code	Full Product Name	可调光
928144709298	MST SON-T PIA PLUS 250W E E40 1SL/12	是	928483300094	MST SON-T PIA Plus 100W E E40	否
928144809298	MST SON-T PIA PLUS 400W E E40 1SL/12	是	928483400093	MASTER SON-T PIA PLUS 150W E E40 1SL/12	否
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	否	928152700028	MST SON-T PIA Plus 70W/220 E27 1SL/12	是

机械和外壳

Order Code	Full Product Name	灯泡外形	Order Code	Full Product Name	灯泡外形
928144709298	MST SON-T PIA PLUS 250W E E40 1SL/12	T46	928483300094	MST SON-T PIA Plus 100W E E40	T46
928144809298	MST SON-T PIA PLUS 400W E E40 1SL/12	T46	928483400093	MASTER SON-T PIA PLUS 150W E E40 1SL/12	T46
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	T46	928152700028	MST SON-T PIA Plus 70W/220 E27 1SL/12	T35

审批和申请

Order Code	Full Product Name	能耗 kWh/ 1000 h	汞 (Hg)	
			含量 (最 高)	汞 (Hg) 含 量 (标称)
928144709298	MST SON-T PIA PLUS 250W E E40 1SL/12	286 kWh	-	15.1 mg
928144809298	MST SON-T PIA PLUS 400W E E40 1SL/12	449 kWh	-	20 mg
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	663 kWh	-	18.9 mg
928483300094	MST SON-T PIA Plus 100W E E40	110 kWh	-	14.3 mg
928483400093	MASTER SON-T PIA PLUS 150W E E40 1SL/12	169 kWh	-	13.9 mg

Order Code	Full Product Name	能耗 kWh/ 1000 h	汞 (Hg)	
			含量 (最 高)	汞 (Hg) 含 量 (标称)
928152700028	MST SON-T PIA Plus 70W/220 E27 1SL/12	73 kWh	12.2 mg	12.2 mg

