



產品說明

MASTER SON-T PIA Plus 高壓鈉燈

本產品為高壓鈉燈管，採用 透明外管，具有高輸出、品質穩定、以及使用壽命長等特色

优点

- 產品採用一流技術製造，具有品質穩定、使用壽命長、高 流明維持率，以及使用期間啟動狀態穩定等特色
- 節能省電效率高，完全不使用 鉛 (Pb)，實為愛護地球首選
- 高流明效率，讓此款 HPS 燈管最為節能省電

特点

- 可調光
- 透明外管
- 採用陶瓷放電管，搭配 飛利浦的整合式天線 (PIA)，不但品質穩定，使用壽命也相當長
- 產品結構堅固耐用，並以最少的焊接點，達到高度防震效果，減少產品提前失效機率，延長燈管使用壽命
- 使用鈷鋅吸收劑，確保高流明維持率，避免燈管提早報銷
- 「Plus」高效率概念，提供更高光量輸出
- 燈管完全無鉛

应用

- 道路與住宅照明
- 裝飾型泛光照明、燈飾
- 工業區域照明
- 室內外休閒運動設施
- 園藝照明

安全提示

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER SON-T PIA Plus 高壓鈉燈

Versions



LPPR SON-TPIA Plus E40

二维绘图



Product	D (max)	O	L	C (max)
MST SON-T PIA Plus 150W/220 E40 - 1SL/12	48 mm	61 mm	132 mm	210 mm
MST SON-T PIA Plus 250W E E40 1SL/12	48 mm	64 mm	158 mm	257 mm
MST SON-T PIA Plus 400W E E40 1SL/12	48 mm	83 mm	175 mm	279 mm

一般資訊	
燈座基底	E40
操作位置	UNIVERSAL
照明技術	
色度坐標 X (標稱)	0.535
相關色溫 (標稱)	2000 K
演色性指數 (CRI)	-
控制與調光	
可調光	是
機械與外罩	
燈泡表層	透明
燈泡形狀	T46

照明技術

Order Code	Full Product Name	色度坐標 Y (Nom)	光效 (額定) (標準)	光通量
928144709230	MST SON-T PIA Plus 250W E E40 1SL/12	0.420	125 lm/W	33,000 lm
928144809227	MST SON-T PIA Plus 400W E E40 1SL/12	0.42	137 lm/W	55,900 lm
928150909230	MST SON-T PIA Plus 150W/220 E40 - 1SL/12	0.42	115.16 lm/W	17,800 lm

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量
928144709230	MST SON-T PIA Plus 250W E E40 1SL/12	109 V	264 W
928144809227	MST SON-T PIA Plus 400W E E40 1SL/12	105 V	408.0 W

Order Code	Full Product Name	電壓 (標稱)	耗電量
928150909230	MST SON-T PIA Plus 150W/220 E40 - 1SL/12	104 V	155.0 W

認證與應用

MASTER SON-T PIA Plus 高壓鈉燈

Order Code	Full Product Name	能源消耗	汞 (Hg) 含量	汞 (Hg) 含量
		kWh/1000 h	(最大)	(標稱)
928144709230	MST SON-T PIA Plus 250W E40 1SL/12	257 kWh	15.1 mg	15.1 mg
928144809227	MST SON-T PIA Plus 400W E40 1SL/12	408 kWh	19.6 mg	20 mg
928150909230	MST SON-T PIA Plus 150W/220 E40 - 1SL/12	155 kWh	15.1 mg	15 mg

