



Environmentally Responsible Lamps

High Output T12

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Benefits

- Sustainable Lighting Solution -Less mercury and fewer lamps in landfills, combined with energy efficiency, reduces the impact on the environment.
- 12 month warranty period.
- TCLP compliant*
- * Fluorescent lamps that are TCLP compliant reduce the amount of pollutants released into the environment.

Features

- ALTO Lamp Technology.
- High light output.
- Available in 35,40,50,55,60,75,80,85,and 100 watts,in daylight, cool white, spec35, and ultralume colors.

Application

- Ideal for use in high bay applications such as warehouses, distribution centers and factories.

High Output T12


Versions



LPPR F-T12-HO RDC GB

Dimensional drawing

| Product |
|-------------------------|
| F96T12/D/HO-O ALTO 15PK |



T12 Reverse Double Contact

