



Continuous light output

Preheat T12

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.


Features

- Available in 14,15 and 20 watts Cool white. 15 and 20 watt Daylight. 20 watt Ultralume. 20 watt Colortone. 20 watt Warm White and Plant light.

Application

- Ideal for use in under cabinet lighting and specialty appliance applications.


Versions



LPPR F-T12-PH G13 ALC

Preheat T12

Dimensional drawing



General Information	
Cap-Base	G13
Mechanical and Housing	
Bulb Shape	T-12

Light Technical

Order Code	Full Product Name	Color Designation	Correlated		
			Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
927883002901	F20T12/W W ALTO 30PK	Warm White (WW)	3000 K	53	1,250 lm
927883003301	F20T12/CW ALTO 30PK	Cool White (CW)	4100 K	62	1,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
927883002901	F20T12/WW ALTO 30PK	20 W
927883003301	F20T12/CW ALTO 30PK	20 W

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
927883002901	F20T12/WW ALTO 30PK	1.9 mg
927883003301	F20T12/CW ALTO 30PK	1.9 mg

Product
F15T12/CW 30PK
F20T12/CW ALTO 30PK
F20T12/D ALTO 30PK
F20T12/WW ALTO 30PK

Order Code	Full Product Name	Color Designation	Correlated		
			Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
927883005405	F20T12/D ALTO 30PK	Daylight	6500 K	73	1,075 lm
927882003311	F15T12/CW 30PK	Cool White (CW)	4100 K	62	800 lm

Order Code	Full Product Name	Power Consumption
927883005405	F20T12/D ALTO 30PK	20 W
927882003311	F15T12/CW 30PK	15 W

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
927883005405	F20T12/D ALTO 30PK	1.7 mg
927882003311	F15T12/CW 30PK	8.0 mg

Preheat T12

