



# Environmentally Responsible Lamps

## Rapid Start T12

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

### Benefits

- Sustainable Lighting Solution -Less mercury and fewer lamps in landfills, combined with energy efficiency, reduces the impact on the environment.
- 12 month warranty period.
- TCLP compliant\*
- \* Fluorescent lamps that are TCLP compliant reduce the amount of pollutants released into the environment.

### Features

- Outstanding Lumen Performance.
- Reduces the impact on the environment.
- Low mercury.
- Available in 34 and 40 watts in various color temperatures.

### Application

- Ideal for commercial applications with 2' x 4' fixtures.


# Rapid Start T12

## Versions




LPPR F-T12-HO RDC GB

## Dimensional drawing



T12 Reversed Double Contact



Mechanical and Housing	
Bulb Shape	T-12

## General Information

Order Code	Full Product Name	Cap-Base
927894705701	F96T12/DX/HO/ALTO 15PK	R17d (RDC)
927886002905	F30T12/WW/RS ALTO 30PK	G13
927886003305	F30T12/CW/RS ALTO 30PK	G13

Product
F96T12/DX/HO/ALTO 15PK

Product
F30T12/CW/RS ALTO 30PK
F30T12/D/RS ALTO 30PK
F30T12/WW/RS ALTO 30PK
F40DX ALTO 30PK
F40T12/CWX/ALTO 30PK

## Light Technical

Rapid Start T12

Order Code	Full Product		Correlated	Color	Luminous
	Name	Designation	Color Temperature (Nom)	rendering index (CRI)	
927894705701	F96T12/DX/HO/ALTO 15PK	-	6500 K	90	6,750 lm
927886002905	F30T12/WW/RS ALTO 30PK	Warm White (WW)	3000 K	53	2,300 lm
927886003305	F30T12/CW/RS ALTO 30PK	Cool White (CW)	4100 K	62	2,250 lm

Order Code	Full Product		Correlated	Color	Luminous
	Name	Designation	Color Temperature (Nom)	rendering index (CRI)	
927886005403	F30T12/D/R S ALTO 30PK	Daylight	6500 K	79	1,950 lm
927888003723	F40T12/CW X/ALTO 30PK	Deluxe Cool White	4100 K	89	2,200 lm
927888005709	F40DX ALTO 30PK	Daylight Deluxe	6500 K	90	2,325 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
927894705701	F96T12/DX/HO/ALTO 15PK	110 W
927886002905	F30T12/WW/RS ALTO 30PK	30 W
927886003305	F30T12/CW/RS ALTO 30PK	30 W

Order Code	Full Product Name	Power Consumption
927886005403	F30T12/D/RS ALTO 30PK	30 W
927888003723	F40T12/CWX/ALTO 30PK	40 W
927888005709	F40DX ALTO 30PK	40 W

Approval and Application

Order Code	Full Product Name	Energy Saving	Mercury (Hg)
		Product	Content (Nom)
927894705701	F96T12/DX/HO/ALTO 15PK	-	6.8 mg
927886002905	F30T12/WW/RS ALTO 30PK	Not Applicable	3.5 mg
927886003305	F30T12/CW/RS ALTO 30PK	Not Applicable	3.5 mg

Order Code	Full Product Name	Energy Saving	Mercury (Hg)
		Product	Content (Nom)
927886005403	F30T12/D/RS ALTO 30PK	Not Applicable	4.4 mg
927888003723	F40T12/CWX/ALTO 30PK	Not Applicable	4.4 mg
927888005709	F40DX ALTO 30PK	Not Applicable	4.4 mg

