



Environmentally Responsible Lamps

U-Bent Rapid Start T12

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Benefits

- Sustainable Lighting Solution -Less mercury and fewer lamps in landfills, combined with energy efficiency, reduces the impact on the environment.
- 12 month warranty period.
- TCLP compliant*
- * Fluorescent lamps that are TCLP compliant reduce the amount of pollutants released into the environment.

Features

- Full Line of 6" Leg Spacing.
- Outstanding Lumen Performance.
- Reduces the impact on the environment.
- Low mercury.

Application

- Ideal for commercial applications with 2' x 2' fixtures.

U-Bent Rapid Start T12

Versions



LPPR F-T12-UR G13 ALC

Dimensional drawing

Product
FB40DX/6 12PK

