



High performance, extra low mercury

Advantage T8

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

Benefits

- Reduced impact on the environment without sacrificing performance
- Better for the environment--only 1.7mg of mercury with ALTO II Technology

Features

- High lumens enable multiple system options to maximize energy savings and reduce lighting costs
- Fully dimmable without burn-in
- Available in multiple wattages: 17W, 25W, and 32W
- Available in multiple color temperatures: 3000K, 3500K, 4100K & 5000K

Application


- Ideal for applications requiring maximum light output.

Warnings and Safety

- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Advantage T8

Dimensional drawing



Product
F32T8/ADV830 ALTO 30PK
F32T8/ADV835 ALTO 30PK
F32T8/ADV841 ALTO 30PK
F32T8/ADV850 ALTO 30PK

General Information	
Cap-Base	G13
Light Technical	
Luminous Flux	3,000 lm
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Bulb Shape	T-8
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)
927869783102	F32T8/ADV830 ALTO 30PK	Advantage 830	3000 K	85
927869783603	F32T8/ADV835 ALTO 30PK	Advantage 835	3500 K	85

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)
927869784203	F32T8/ADV841 ALTO 30PK	Advantage 841	4100 K	85
927869785102	F32T8/ADV850 ALTO 30PK	Advantage 850	5000 K	82

