



Reduce your maintenance costs

PLUS T8 High Output

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Benefits

- Low mercury – only 4.4 mg per lamps.
- 24 month Warranty Period.
- TCLP Compliant*
- * Fluorescent lamps that are TCLP Compliant reduce the amount of pollutants released into the environment.

Features

- Extends the relamping cycle which reduces maintenance and disposal costs.
- PLUS T8 HO 8-foot has the longest rated average life in the industry.
- 30,000 hours rated average life \diamond
- More light over life with 95% lumen maintenance than a MH 400/U at 67% lumen maintenance.
- Available in 8 foot length 86 watts with 3000, 3500 & 4100 Color Temperatures.
- \diamond Average life under engineering data with lamps turned off and restarted once every 12 operating hours.

Application

- Ideal for industrial applications requiring longer life.

PLUS T8 High Output


Versions



LPPR F-T8-HOP RDC GB

Dimensional drawing

Product
F96T8/TL841/HO/PLUS ALTO 25/1
F96T8/TL850/PLUS/HO/ALTO 25/1



General Information	
Cap-Base	R17d (RDC)
Light Technical	
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	86 W
Mechanical and Housing	
Bulb Shape	T-8
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg

Light Technical

Order Code	Full Product Name	Color	Correlated Color	Luminous Flux
		Designation	Temperature (Nom)	
927874084105	F96T8/TL841/HO/ PLUS ALTO 25/1	TL841	4100 K	8,200 lm

PLUS T8 High Output

Order Code	Full Product Name	Color	Correlated Color	
		Designation	Temperature (Nom)	Luminous Flux
927874085005	F96T8/TL850/ PLUS/HO/ALTO 25/1	TL850	5000 K	8,100 lm

