



Retail Sales T8

Retail Sales T8

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Versions




15W T8 Soft White Tubular
Fluorescent - RFT



15W T8 Cool White Tubular
Fluorescent - RFT

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
15W T8 Cool White Tubular Fluorescent	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
15W T8 Soft White Tubular Fluorescent	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Retail Sales T8

General Information	
Cap-Base	G13
Operating and Electrical	
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V
Power Consumption	15 W
Wattage Equivalent	15 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg

Light Technical

Order Code	Full Product Name	Color	Correlated Color	Color	Luminous
		Designation	Temperature (Nom)	rendering index (CRI)	
928022883028	15W T8 Soft White Tubular Fluorescent	Soft White	3000 K	83	990 lm
928022803328	15W T8 Cool White Tubular Fluorescent	Cool White (CW)	4100 K	63	830 lm

