



Powerful, Comprehensive and Reliable

GreenUp Grid

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Grid product family offers a complete range of options with comprehensive control availability, optical solutions and powerful lumen outputs, meanwhile ensures the product reliability and quality within compact luminaire body.

Benefits

- Comprehensive offerings to meet various application requirements.
- Compact body while delivering powerful lumen outputs.
- Good glare control with color rendering performance.
- Ensured quality and reliability.

Features

- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- Tilttable & rotatable
- UGR19 & CRI90

Application



- Retail
- Hospitality
- Fashion

Versions



GreenUp Grid

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Optical cover type	Acrylate
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical		Correlated Color	Luminous Efficacy	Luminous Flux
Order Code	Full Product Name	Temperature (Nom)	(rated) (Nom)	
53089899	GD309B 3*P20 930 PSU-E MB	3000 K	90 lm/W	5,400 lm
52965699	GD309B 3*P20 930 PSU-E WB	3000 K	94 lm/W	5,640 lm
52474399	GD309B 3*P20 940 PSU-E NB	4000 K	96 lm/W	5,760 lm
52430999	GD309B 3*P20 940 PSU-E VWB	4000 K	80 lm/W	4,800 lm
52500999	GD309B 3*P24 940 PSU-E MB	4000 K	93 lm/W	6,700 lm
52936699	GD309B 3*P33 930 PSU-E MB	3000 K	86 lm/W	8,510 lm
52717199	GD309B 3*P33 940 PSU-E WB	4000 K	98 lm/W	9,700 lm
53122299	GD309B 3*P33 940 PSD-E NB	4000 K	95 lm/W	9,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
53089899	GD309B 3*P20 930 PSU-E MB	54 W
52965699	GD309B 3*P20 930 PSU-E WB	54 W
52474399	GD309B 3*P20 940 PSU-E NB	54 W
52430999	GD309B 3*P20 940 PSU-E VWB	54 W

Order Code	Full Product Name	Power Consumption
52500999	GD309B 3*P24 940 PSU-E MB	64.8 W
52936699	GD309B 3*P33 930 PSU-E MB	108.9 W
52717199	GD309B 3*P33 940 PSU-E WB	108.9 W
53122299	GD309B 3*P33 940 PSD-E NB	108.9 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
53089899	GD309B 3*P20 930 PSU-E MB	No
52965699	GD309B 3*P20 930 PSU-E WB	No
52474399	GD309B 3*P20 940 PSU-E NB	No
52430999	GD309B 3*P20 940 PSU-E VWB	No

Order Code	Full Product Name	Dimmable
52500999	GD309B 3*P24 940 PSU-E MB	No
52936699	GD309B 3*P33 930 PSU-E MB	No
52717199	GD309B 3*P33 940 PSU-E WB	No
53122299	GD309B 3*P33 940 PSD-E NB	Yes

