



Spot of crisp white light – modern alternative to conventional reflector lamps

HalogenA PAR38

Mains-voltage halogen reflector that is easy to install instead of conventional reflector lamps, putting your objects in a superior-quality spot light. Provides crisp halogen light over a long lifetime.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


HalogenA PAR38

Versions




8711500887788 - RFT


Dimensional drawing



Product	D (max)	C (max)
100 W E27 cap Dimmable Halogen reflector bulb	121 mm	135.5 mm




Accent Diagrams



Accent Diagram - HalogenA PAR38 100W E27
120V 30D 1CT/15

HalogenA PAR38

Beam Diagrams



Beam diagram - HalogenA PAR38 100W E27
120V 30D 1CT/15

