



The new classic light bulb

Halogen Classic A-shape

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Benefits

- Identical look and feel to standard lamp, with bright, sparkling halogen light
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Double the lifetime of a standard bulb and immediate light when switching on

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

Application

- Accent and general lighting applications in homes, offices, shops, hotels and restaurants. Replacement for traditional bulb in classical luminaires

Halogen Classic A-shape

Versions





LPPR ECOCLAB 0007



8718291205722 - RFT

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 105W B22 240V A55 FR 1CT/10	56 mm	95.5 mm
EcoClassic 140W B22 240V A55 FR 1CT/10	56 mm	95.5 mm

Product	D (max)	C (max)
70 W (100 W) E27 cap Warm white Halogen bulb	51 mm	91 mm

Halogen Classic A-shape

General Information	
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes

General Information

Order Code	Full Product Name	Cap-Base
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	B22
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	B22
925699536301	70 W (100 W) E27 cap Warm white Halogen bulb	E27

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	LLMF At		Luminous Flux
			End Of Nominal Lifetime (Nom)	Luminous Efficacy (rated) (Nom)	
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	2800 K	-	18.9 lm/W	1,980 lm
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	2800 K	-	20.3 lm/W	2,840 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	LLMF At		Luminous Flux
			End Of Nominal Lifetime (Nom)	Luminous Efficacy (rated) (Nom)	
925699536301	70 W (100 W) E27 cap Warm white Halogen bulb	2900 K	85 %	16.9 lm/W	1,180 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	0.44 A	240 V	105 W
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	0.58 A	240 V	140 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
925699536301	70 W (100 W) E27 cap Warm white Halogen bulb	0.58 A	120 V	70 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	Frosted	A55
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	Frosted	A55

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925699536301	70 W (100 W) E27 cap Warm white Halogen bulb	White	E50

Halogen Classic A-shape

