



# The new halogen mains-voltage capsule. Compact shape, crisp white light

## Halogen Clickline G9

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

### Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Compact size, easy to fit in the luminaire
- Universal burning position
- Instant start

### Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums. Ideal for use in small, decorative luminaires


# Halogen Clickline G9

## Versions



8718291204244 - RFT

## Dimensional drawing



Product	D (max)	L	C (max)
28 W (40 W) G9 cap Warm white Halogen capsule bulb	13 mm	21.7 mm	45 mm
Halogen MV Click 19.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 29.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

General Information	
Cap-Base	G9
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13

## Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated)	
		(Nom)	Luminous Flux
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	12.1 lm/W	370 lm
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	11.1 lm/W	204 lm
925640644202	28 W (40 W) G9 cap Warm white Halogen capsule bulb	12.1 lm/W	370 lm

## Operating and Electrical

# Halogen Clickline G9

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	0.12 A	28.0 W
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	0.08 A	18 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925640644202	28 W (40 W) G9 cap Warm white Halogen capsule bulb	0.12 A	28.0 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	28 kWh
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	18 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
925640644202	28 W (40 W) G9 cap Warm white Halogen capsule bulb	28 kWh

