



產品說明

HF-Selectalume II for TL-D lamps

價格合理、品質可靠、符合 CE 的 TL-D 螢光燈管專用高頻電子安定器，是電磁 (EM) 安定器的理想替代產品

优点

- Exceptional energy efficiency with striation-reduction technology in lighting systems at lower temperatures
- Maximum reliability in system operation
- Provides extended lamp life in frequent-switching applications

特点

- Highest CELMA Energy Efficiency Index A2 BAT*
- Complies with CE, ENEC, EL, VDE-EMC, CCC marks of conformity
- Average nominal service lifetime over 85,000 hours (at Ta 50°C) with a failure rate $\leq 0.1\%$ per 1,000 hours)
- Optimized lamp preheating for min 50,000 On/Off switch operations without replacement of lamps

应用

- 如欲降低每平方公尺瓦數或減少營運成本，即十分適用，常見的照明用途如下：
- 非常適合未安裝控制裝置的應用。
- 運作時數長的專業室內應用（例如辦公大樓、客服中心、教室和旅館）
- 百貨公司、商店、超市、便利商店和
- 運作時數長的工業場所（例如走廊和低隔間管道系統）
- 市區停車場


HF-Selectalume II for TL-D lamps

Versions



GPPR_HFSIITL5_0005-Product photo

二维绘图



Product

HF-S 3/4 18 TL-D II 220-240V 50/60Hz

Product	A1	B1	C1	A2	B2	D1
HF-S 3/4 18 TL-D II 220-240V 50/60Hz	280 mm	39 mm	28 mm	265 mm		4.2 mm

