



Philips Twistline GU10

Twistline GU10

Bright, white accent light with superior energy savings. Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.

Benefits

- Easy to install and maintain a secure fit.
- Highlight art and featured objects for decorative accent.

Features

- Bright, white light.
- Easy to use twist and lock base.
- Available in a variety of wattages operating on 120 volts.
- Available in 25,35 and 50 Watts.

Application

- Ideal for indoor recessed and track fixtures, floor and desk lamps.

Versions



35W GU10 Sparkling light Mini-Reflector - RFT



25W MR16 GU10 Base Indoor Flood Light - RFT


Twistline GU10

Versions



50W GU10 Sparkling light
Reflector - RFT

Dimensional drawing



Product	D (max)	C (max)
25W MR16 GU10 Base Indoor Flood Light	50.7 mm	53 mm
35W GU10 Sparkling light Dimmable Mini-Reflector	50.7 mm	53 mm
50W GU10 Sparkling light Dimmable Reflector	51 mm	53 mm

General Information	
Cap-Base	GU10
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	120 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16


Light Technical

Order Code	Full Product Name	Beam Angle (Nom)
924887136384	35W GU10 Sparkling light Dimmable Mini-Reflector	20 degree(s)
924887736301	25W MR16 GU10 Base Indoor Flood Light	25 degree(s)
925691836309	50W GU10 Sparkling light Dimmable Reflector	25 degree(s)


Operating and Electrical

Twistline GU10

Order Code	Full Product Name	Power Consumption
924887136384	35W GU10 Sparkling light Dimmable Mini-Reflector	35 W
924887736301	25W MR16 GU10 Base Indoor Flood Light	25 W
925691836309	50W GU10 Sparkling light Dimmable Reflector	50 W




Accent Diagrams



Accent Diagram - BC50GU10/HAL/TL 120V 6/3

Beam Diagrams



Beam diagram - BC50GU10/HAL/TL 120V 6/3

