



Product Description

Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 clear

Versions






LPPR ICANBSTD B22 B35 CL



LPPR_ICANESTD_E27_B35_CL-
Product photo

Dimensional drawing



Product	D	C (max)
230V 25W CANDLE BC CLEAR	35 mm	94.5 mm

Product	D	C (max)
Stan 25W E14 220-240V B35 CL 1CT/5X10F	35 mm	100 mm
Stan 25W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm
Stan 40W E14 220-240V B35 CL 1CT/5X10F	35 mm	100 mm
Stan 40W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm
Stan 40W E14 230V B35 CL U 1CT/6X50CT	35 mm	100 mm
Stan 60W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm

Product	D	C (max)
Stan 40W E27 230V B35 CL 1CT/10X10F	35 mm	96.5 mm

Standard Candle B35 clear

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35

General Information

Order Code	Full Product Name	Cap-Base
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	E14
921486544204	Stan 25W E14 230V B35 CL 1CT/10X10F	E14
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	E14
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	E14

Order Code	Full Product Name	Cap-Base
926000006814	Stan 40W E14 230V B35 CL 1CT/10X10F	E14
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	E14
921485544299	230V 25W CANDLE BC CLEAR	B22
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	E27

Light Technical

Order Code	Full Product Name	Luminous Flux
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	210 lm
921486544204	Stan 25W E14 230V B35 CL 1CT/10X10F	215 lm
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	410 lm
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	670 lm

Order Code	Full Product Name	Luminous Flux
926000006814	Stan 40W E14 230V B35 CL 1CT/10X10F	410 lm
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	410 lm
921485544299	230V 25W CANDLE BC CLEAR	205 lm
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	390 lm

Operating and Electrical

Order Code	Full Product Name	Power	
		Voltage (Nom)	Consumption
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	220-240 V	25 W
921486544204	Stan 25W E14 230V B35 CL 1CT/10X10F	230 V	25 W
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	220-240 V	40 W
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	230 V	60 W

Order Code	Full Product Name	Power	
		Voltage (Nom)	Consumption
926000006814	Stan 40W E14 230V B35 CL 1CT/10X10F	230 V	40 W
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	230 V	40 W
921485544299	230V 25W CANDLE BC CLEAR	230 V	25 W
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	230 V	40 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	-
921486544204	Stan 25W E14 230V B35 CL 1CT/10X10F	Yes
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	Yes
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	Yes

Order Code	Full Product Name	Dimmable
926000006814	Stan 40W E14 230V B35 CL 1CT/10X10F	Yes
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	Yes
921485544299	230V 25W CANDLE BC CLEAR	Yes
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	Yes

Standard Candle B35 clear

