



Product Description

Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with E-base

Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches



Standard Candle B35 clear

Versions



LPPR_ICANESTD_E27_B35_CL-
Product photo

Dimensional drawing



| Product | D | C (max) |
|-------------------------------------|-------|---------|
| Stan 25W E14 230V B35 CL 1CT/10X10F | 35 mm | 100 mm |
| Stan 40W E14 230V B35 CL 1CT/10X10F | 35 mm | 100 mm |
| Stan 60W E14 230V B35 CL 1CT/10X10F | 35 mm | 100 mm |

| Product | D | C (max) |
|-------------------------------------|-------|---------|
| Stan 40W E27 230V B35 CL 1CT/10X10F | 35 mm | 96.5 mm |

Standard Candle B35 clear

| General Information | |
|-----------------------------|---------------|
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Nominal lifetime | 1,000 hour(s) |
| Operating Position | UNIVERSAL |
| Light Technical | |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Voltage (Nom) | 230 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | B35 |

General Information

| Order Code | Full Product Name | Cap-Base |
|------------|-------------------------------------|----------|
| 01160250 | STAN 25W E14 230V B35 CL 1CT/10X10F | E14 |
| 01167150 | STAN 60W E14 230V B35 CL 1CT/10X10F | E14 |
| 01163350 | STAN 40W E14 230V B35 CL 1CT/10X10F | E14 |
| 05669650 | STAN 40W E27 230V B35 CL 1CT/10X10F | E27 |

Light Technical

| Order Code | Full Product Name | Luminous Flux |
|------------|-------------------------------------|---------------|
| 01160250 | STAN 25W E14 230V B35 CL 1CT/10X10F | 215 lm |
| 01167150 | STAN 60W E14 230V B35 CL 1CT/10X10F | 670 lm |

| Order Code | Full Product Name | Luminous Flux |
|------------|-------------------------------------|---------------|
| 01163350 | STAN 40W E14 230V B35 CL 1CT/10X10F | 410 lm |
| 05669650 | STAN 40W E27 230V B35 CL 1CT/10X10F | 390 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|------------|-------------------------------------|-------------------|
| 01160250 | STAN 25W E14 230V B35 CL 1CT/10X10F | 25 W |
| 01167150 | STAN 60W E14 230V B35 CL 1CT/10X10F | 60 W |

| Order Code | Full Product Name | Power Consumption |
|------------|-------------------------------------|-------------------|
| 01163350 | STAN 40W E14 230V B35 CL 1CT/10X10F | 40 W |
| 05669650 | STAN 40W E27 230V B35 CL 1CT/10X10F | 40 W |

