



Product Description

Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches


Standard Candle B35 clear

Versions



LPPR1_ICANESTD_E14_B35_CL.JPG

Dimensional drawing



Product	D	C (max)
Stan 25W E14 220-240V B35 CL 1CT/5X10F	35 mm	100 mm
Stan 40W E14 220-240V B35 CL 1CT/5X10F	35 mm	100 mm

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	220-240 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35

Light Technical

Order Code	Full Product Name	Luminous Flux
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	210 lm
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	25 W

Order Code	Full Product Name	Power Consumption
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	40 W

Controls and Dimming

Standard Candle B35 clear

Order Code	Full Product Name	Dimmable
921486543301	Stan 25W E14 220-240V B35 CL 1CT/5X10F	-

Order Code	Full Product Name	Dimmable
921491543301	Stan 40W E14 220-240V B35 CL 1CT/5X10F	Yes

