



Product Description

Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 clear

Versions





LPPR1_ICANESTD_E14_B35_CL.JPG



LPPR ICANBSTD B22 B35 CL

Dimensional drawing



Product	D	C (max)
230V 25W CANDLE BC CLEAR	35 mm	94.5 mm

Product	D	C (max)
Stan 40W E14 230V B35 CL U 1CT/6X50CT	35 mm	100 mm

Standard Candle B35 clear

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35

General Information

Order Code	Full Product Name	Cap-Base
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	E14
921485544299	230V 25W CANDLE BC CLEAR	B22

Light Technical

Order Code	Full Product Name	Luminous Flux
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	410 lm

Order Code	Full Product Name	Luminous Flux
921485544299	230V 25W CANDLE BC CLEAR	205 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	40 W

Order Code	Full Product Name	Power Consumption
921485544299	230V 25W CANDLE BC CLEAR	25 W

