



Product Description

Standard Candle B35 frosted

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

Features

- Slender, frosted lamps
- Creates a low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 frosted

Versions






LPPR ICANBSTD B22 B35 CL



LPPR_ICANESTD_E27_B35_FR-
Product photo

Dimensional drawing



Product	D	C (max)
230V 25W BC PEARL CANDLE	35 mm	95 mm

Product	D	C (max)
Stan 25W E14 220-240V B35 FR 1CT/5X10F	35 mm	100 mm
Stan 40W E14 230V B35 FR 1CT/10X10F	35 mm	100 mm
Stan 40W E14 230V B35 FR U 1CT/6X50CT	35 mm	100 mm
Stan 60W E14 230V B35 FR 1CT/10X10F	35 mm	100 mm

Product	D	C (max)
Stan 40W E27 230V B35 FR 1CT/10X10F	35 mm	96.5 mm

Standard Candle B35 frosted

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35

General Information

Order Code	Full Product Name	Cap-Base	Order Code	Full Product Name	Cap-Base
921486643301	Stan 25W E14 220-240V B35 FR 1CT/5X10F	E14	926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	E14
926000006918	Stan 40W E14 230V B35 FR 1CT/10X10F	E14	921485644299	230V 25W BC PEARL CANDLE	B22
926000007764	Stan 60W E14 230V B35 FR 1CT/10X10F	E14	921492144218	Stan 40W E27 230V B35 FR 1CT/10X10F	E27

Light Technical

Order Code	Full Product Name	Luminous Flux	Order Code	Full Product Name	Luminous Flux
921486643301	Stan 25W E14 220-240V B35 FR 1CT/5X10F	210 lm	926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	410 lm
926000006918	Stan 40W E14 230V B35 FR 1CT/10X10F	410 lm	921485644299	230V 25W BC PEARL CANDLE	205 lm
926000007764	Stan 60W E14 230V B35 FR 1CT/10X10F	670 lm	921492144218	Stan 40W E27 230V B35 FR 1CT/10X10F	390 lm

Operating and Electrical

Order Code	Full Product Name	Power		Order Code	Full Product Name	Power	
		Voltage (Nom)	Consumption			Voltage (Nom)	Consumption
921486643301	Stan 25W E14 220-240V B35 FR 1CT/5X10F	220-240 V	25 W	926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	230 V	40 W
926000006918	Stan 40W E14 230V B35 FR 1CT/10X10F	230 V	40 W	921485644299	230V 25W BC PEARL CANDLE	230 V	25 W
926000007764	Stan 60W E14 230V B35 FR 1CT/10X10F	230 V	60 W	921492144218	Stan 40W E27 230V B35 FR 1CT/10X10F	230 V	40 W

