



Product Description

Standard Candle B35 frosted

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with E-base

Benefits

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

Features

- Slender, frosted lamps
- Creates a low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches


Standard Candle B35 frosted

Versions



LPPR_ICANESTD_E14_B35_FR-
Product photo

Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V B35 FR 1CT/10X10F	35 mm	100 mm
Stan 60W E14 230V B35 FR 1CT/10X10F	35 mm	100 mm

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35

Light Technical

Order Code	Full Product Name	Luminous Flux
01133650	STAN 40W E14 230V B35 FR 1CT/10X10F	410 lm
01176350	STAN 60W E14 230V B35 FR 1CT/10X10F	670 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
01133650	STAN 40W E14 230V B35 FR 1CT/10X10F	40 W

Order Code	Full Product Name	Power Consumption
01176350	STAN 60W E14 230V B35 FR 1CT/10X10F	60 W

Standard Candle B35 frosted

