



Product Description

Standard Candle B35 frosted

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

Features

- Slender, frosted lamps
- Creates a low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 frosted

Versions





LPPR_ICANESTD_E14_B35_FR-
Product photo



LPPR ICANBSTD B22 B35 CL

Dimensional drawing



Product	D	C (max)
230V 25W BC PEARL CANDLE	35 mm	95 mm

Product	D	C (max)
Stan 40W E14 230V B35 FR U 1CT/6X50CT	35 mm	100 mm

Standard Candle B35 frosted

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35

General Information

Order Code	Full Product Name	Cap-Base
926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	E14
921485644299	230V 25W BC PEARL CANDLE	B22

Light Technical

Order Code	Full Product Name	Luminous Flux
926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	410 lm

Order Code	Full Product Name	Luminous Flux
921485644299	230V 25W BC PEARL CANDLE	205 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	40 W

Order Code	Full Product Name	Power Consumption
921485644299	230V 25W BC PEARL CANDLE	25 W

