



Product Description

Standard Lustre P45 clear

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Benefits

- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Small, crystal-clear lamps designed for sparkling highlights
- At their best in decorative small luminaires such as table models and wall brackets with clear glass bowls
- Creates a sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

Standard Lustre P45 clear

Versions



LPPR ILUSBSTD B22 P45 CL






GreenSpace Linear Accent



7894400001841 - RFT

Dimensional drawing




Product	D	C (max)
40 W E27 cap 110-127 V Incandescent luster bulb	45 mm	73 mm

Product	D	C (max)
230V 15W GLS CLEAR BAYONET CAP	45 mm	71.5 mm

Product	D	C (max)
Stan 40W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 25W E27 220-240V P45 CL 1CT/5X10F	45 mm	73 mm
Stan 40W E27 220-240V P45 CL 1CT/5X10F	45 mm	73 mm

General Information	
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
921400544299	230V 15W GLS CLEAR BAYONET CAP	B22	-
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	E27	1,000 hour(s)
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	E27	1,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	E14	1,000 hour(s)
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	E27	-

Light Technical

Order Code	Full Product Name	Luminous Flux
921400544299	230V 15W GLS CLEAR BAYONET CAP	110 lm
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	200 lm
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	385 lm

Order Code	Full Product Name	Luminous Flux
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	405 lm
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	455 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Starting Time (Nom)
921400544299	230V 15W GLS CLEAR BAYONET CAP	230 V	15 W	-
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	220-240 V	25 W	-
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	220-240 V	40 W	-

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Starting Time (Nom)
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	230 V	40 W	-
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	127 V	40 W	0.0 s

Standard Lustre P45 clear

Controls and Dimming

Order Code	Full Product Name	Dimmable
921400544299	230V 15W GLS CLEAR BAYONET CAP	Yes
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	Yes
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	Yes

Order Code	Full Product Name	Dimmable
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	Yes
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	-

