



Product Description

Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

Features



- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

Standard Lustre P45 frosted

Dimensional drawing



| Product | D | C (max) |
|-------------------------------------|-------|---------|
| Stan 40W E14 230V P45 FR 1CT/10X10F | 45 mm | 78 mm |
| Stan 60W E14 230V P45 FR 1CT/10X10F | 45 mm | 78 mm |

| Product | D | C (max) |
|--|-------|---------|
| Stan 40W E27 220-240V P45 FR 1CT/5X10F | 45 mm | 73 mm |
| Stan 40W E27 230V P45 FR 1CT/10X10F | 45 mm | 73 mm |
| Stan 60W E27 230V P45 FR 1CT/10X10F | 45 mm | 73 mm |

| General Information | |
|-----------------------------|---------------|
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Nominal lifetime | 1,000 hour(s) |
| Light Technical | |
| Color rendering index (CRI) | 100 |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Shape | P45 |

General Information

| Order Code | Full Product Name | Operating | |
|--------------|--|-----------|-----------|
| | | Cap-Base | Position |
| 921421643301 | Stan 40W E27 220-240V P45 FR 1CT/5X10F | E27 | UNIVERSAL |
| 926000003568 | Stan 60W E27 230V P45 FR 1CT/10X10F | E27 | S90 |

| Order Code | Full Product Name | Operating | |
|--------------|-------------------------------------|-----------|-----------|
| | | Cap-Base | Position |
| 926000003857 | Stan 60W E14 230V P45 FR 1CT/10X10F | E14 | UNIVERSAL |
| 926000007010 | Stan 40W E14 230V P45 FR 1CT/10X10F | E14 | UNIVERSAL |
| 926000007412 | Stan 40W E27 230V P45 FR 1CT/10X10F | E27 | UNIVERSAL |

Light Technical

| Order Code | Full Product Name | Luminous Flux |
|--------------|--|---------------|
| 921421643301 | Stan 40W E27 220-240V P45 FR 1CT/5X10F | 385 lm |

| Order Code | Full Product Name | Luminous Flux |
|--------------|-------------------------------------|---------------|
| 926000003568 | Stan 60W E27 230V P45 FR 1CT/10X10F | 640 lm |

Standard Lustre P45 frosted

| Order Code | Full Product Name | Luminous Flux |
|--------------|-------------------------------------|---------------|
| 926000003857 | Stan 60W E14 230V P45 FR 1CT/10X10F | 650 lm |
| 926000007010 | Stan 40W E14 230V P45 FR 1CT/10X10F | 405 lm |

| Order Code | Full Product Name | Luminous Flux |
|--------------|-------------------------------------|---------------|
| 926000007412 | Stan 40W E27 230V P45 FR 1CT/10X10F | 390 lm |

Operating and Electrical

| Order Code | Full Product Name | Voltage (Nom) | Power |
|--------------|--|---------------|-------------|
| | | | Consumption |
| 921421643301 | Stan 40W E27 220-240V P45 FR 1CT/5X10F | 220-240 V | 40 W |
| 926000003568 | Stan 60W E27 230V P45 FR 1CT/10X10F | 230 V | 60 W |
| 926000003857 | Stan 60W E14 230V P45 FR 1CT/10X10F | 230 V | 60 W |

| Order Code | Full Product Name | Voltage (Nom) | Power |
|--------------|-------------------------------------|---------------|-------------|
| | | | Consumption |
| 926000007010 | Stan 40W E14 230V P45 FR 1CT/10X10F | 230 V | 40 W |
| 926000007412 | Stan 40W E27 230V P45 FR 1CT/10X10F | 230 V | 40 W |

Approval and Application

| Order Code | Full Product Name | Energy Consumption |
|--------------|--|--------------------|
| | | kWh/1000 h |
| 921421643301 | Stan 40W E27 220-240V P45 FR 1CT/5X10F | - |
| 926000003568 | Stan 60W E27 230V P45 FR 1CT/10X10F | 60 kWh |
| 926000003857 | Stan 60W E14 230V P45 FR 1CT/10X10F | 60 kWh |

| Order Code | Full Product Name | Energy Consumption |
|--------------|-------------------------------------|--------------------|
| | | kWh/1000 h |
| 926000007010 | Stan 40W E14 230V P45 FR 1CT/10X10F | - |
| 926000007412 | Stan 40W E27 230V P45 FR 1CT/10X10F | - |

