



Product Description

Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E-base

Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

Features



- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm
Stan 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm

Product	D	C (max)
Stan 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm
Stan 60W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45

General Information

Order Code	Full Product Name	Cap-Base	Operating Position
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	E27	S90
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL

Order Code	Full Product Name	Cap-Base	Operating Position
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	E27	UNIVERSAL

Light Technical

Standard Lustre P45 frosted

Order Code	Full Product Name	Luminous Flux
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	640 lm
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	650 lm

Order Code	Full Product Name	Luminous Flux
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	405 lm
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	390 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	60 W
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	60 W

Order Code	Full Product Name	Power Consumption
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	40 W
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	40 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	60 kWh
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	60 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	-
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	-

