



# Product Description

## Standard A-shape frosted

Conventional pear-shaped incandescent lamps

### Benefits

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of pearl lamp
- Universal burning position


### Features

- Vacuum-filled (15W) or gas-filled (25W and above)

### Application

- Frosted lamps give low glare and diffused lighting for universal applicability

## Dimensional drawing



Product	D	C (max)
Stan 100W B22 240V A55 FR 1CT/10X10F	55 mm	95.5 mm
Stan 60W B22 230V A55 FR 1CT/10X10F	55 mm	95.5 mm
Stan 60W B22 240V A55 FR 1CT/10X10F	55 mm	95.5 mm

Standard A-shape frosted

Dimensional drawing



Product	D (max)	D	C (max)
Stan 60W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 FR 1CT/12X10F	56 mm	55 mm	97 mm
Stan 75W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm

General Information	
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
920054736379	Stan 60W E27 120V A55 FR U 1CT/10X10F	E27	-	-
920055636379	Stan 75W E27 120V A55 FR U 1CT/10X10F	E27	-	-
926000007317	Stan 60W E27 230V A55 FR 1CT/12X10F	E27	1,000 hour(s)	1,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
920054445578	Stan 60W B22 240V A55 FR 1CT/10X10F	B22	-	1,000 hour(s)
920056945581	Stan 100W B22 240V A55 FR 1CT/10X10F	B22	-	1,000 hour(s)
926000008125	Stan 60W B22 230V A55 FR 1CT/10X10F	B22	-	1,000 hour(s)

Light Technical

Order Code	Full Product Name	Luminous Flux
920054736379	Stan 60W E27 120V A55 FR U 1CT/10X10F	-
920055636379	Stan 75W E27 120V A55 FR U 1CT/10X10F	-
926000007317	Stan 60W E27 230V A55 FR 1CT/12X10F	710 lm

Order Code	Full Product Name	Luminous Flux
920054445578	Stan 60W B22 240V A55 FR 1CT/10X10F	700 lm
920056945581	Stan 100W B22 240V A55 FR 1CT/10X10F	1,330 lm
926000008125	Stan 60W B22 230V A55 FR 1CT/10X10F	710 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
920054736379	Stan 60W E27 120V A55 FR U 1CT/10X10F	120 V	60 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
920055636379	Stan 75W E27 120V A55 FR U 1CT/10X10F	120 V	75 W

Standard A-shape frosted

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
926000007317	Stan 60W E27 230V A55 FR 1CT/12X10F	230 V	60 W
920054445578	Stan 60W B22 240V A55 FR 1CT/10X10F	240 V	60 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
920056945581	Stan 100W B22 240V A55 FR 1CT/10X10F	240 V	100 W
926000008125	Stan 60W B22 230V A55 FR 1CT/10X10F	230 V	60 W

