



# Product Description

## Standard A-shape frosted

Conventional pear-shaped incandescent lamps

### Benefits

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of pearl lamp
- Universal burning position

### Features

- Vacuum-filled (15W) or gas-filled (25W and above)

### Application

- Frosted lamps give low glare and diffused lighting for universal applicability

### Versions



LED Lamps, CorePro LEDspotMV E27 R80

# Standard A-shape frosted

## Dimensional drawing



Product	D (max)	D	C (max)
Stan 60W E27 230V A55 FR 1CT/12X10F	56 mm	55 mm	97 mm

