



# Product Description

## Standard A-shape frosted

Conventional pear-shaped incandescent lamps

### Benefits

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of pearl lamp
- Universal burning position


### Features

- Vacuum-filled (15W) or gas-filled (25W and above)

### Application

- Frosted lamps give low glare and diffused lighting for universal applicability

## Dimensional drawing



Product	D	C (max)
Stan 100W B22 240V A55 FR 1CT/10X10F	55 mm	95.5 mm
Stan 60W B22 230V A55 FR 1CT/10X10F	55 mm	95.5 mm
Stan 60W B22 240V A55 FR 1CT/10X10F	55 mm	95.5 mm

Standard A-shape frosted

General Information	
Cap-Base	B22
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55

Light Technical

Order Code	Full Product Name	Luminous Flux
920054445578	Stan 60W B22 240V A55 FR 1CT/10X10F	700 lm
920056945581	Stan 100W B22 240V A55 FR 1CT/10X10F	1,330 lm

Order Code	Full Product Name	Luminous Flux
926000008125	Stan 60W B22 230V A55 FR 1CT/10X10F	710 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
920054445578	Stan 60W B22 240V A55 FR 1CT/10X10F	240 V	60 W
920056945581	Stan 100W B22 240V A55 FR 1CT/10X10F	240 V	100 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
926000008125	Stan 60W B22 230V A55 FR 1CT/10X10F	230 V	60 W

