



Product Description

Standard A-shape clear

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect

Features

- Vacuum-filled (15W) or gas-filled (25W and above)

Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare



Versions



LPPR_ISTDAB_B22_A55_CL-Product photo

Standard A-shape clear

Dimensional drawing



Product	D	C (max)
Stan 100W B22 220-240V A55 CL 1CT/5X10F	55 mm	95.5 mm

Product	D (max)	D	C (max)
Stan 100W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 100W E27 220V A55 CL U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 40W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 60W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm

General Information	
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
920053843301	Stan 40W E27 220-240V A55 CL 1CT/5X10F	E27	-
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	E27	-
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	E27	-

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	E27	-
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)
920056043301	Stan 100W B22 220-240V A55 CL 1CT/5X10F	B22	-

Light Technical

Standard A-shape clear

Order Code	Full Product Name	Luminous Flux
920053843301	Stan 40W E27 220-240V A55 CL 1CT/5X10F	415 lm
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	710 lm
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	1,340 lm

Order Code	Full Product Name	Luminous Flux
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	1,340 lm
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	710 lm
920056043301	Stan 100W B22 220-240V A55 CL 1CT/5X10F	1,340 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power
			Consumption
920053843301	Stan 40W E27 220-240V A55 CL 1CT/5X10F	220-240 V	40 W
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	220-240 V	60 W
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	220 V	100 W

Order Code	Full Product Name	Voltage (Nom)	Power
			Consumption
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	220-240 V	100 W
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	230 V	60 W
920056043301	Stan 100W B22 220-240V A55 CL 1CT/5X10F	220-240 V	100 W

