



Product Description

Deco Tubular

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

Benefits

- Give brilliant and decorative lighting effects
- Ideal for creating a comfortable and relaxing ambience

Features

- Internal coating cannot chip, fade, become scratched or weathered

Application

- General lighting: switchboards, cupboards, piano and painting lighting
- Clear lamps:
- industrial/professional lighting: sign boards, elevator sign systems, fair and festive lighting
- Lamps with inside-frosted bulb:
- ideal for a wide range of domestic and industrial applications


Versions



10 W E14 cap Incandescent tubular
bulb - RFT

Deco Tubular

Dimensional drawing



Product	D (max)	C (max)
10 W E14 cap Clear Incandescent tubular bulb	17 mm	54 mm
7 W E14 cap Clear Incandescent tubular bulb	17 mm	54 mm

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Switching Cycle	4,000
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T17

Light Technical

Order Code	Full Product Name	Luminous Flux
25008750	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	21 lm
03821050	DECO 10W E14 240-250V T17 CL 1CT/10X10F	37 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
25008750	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	0.03 A	230-240 V	7 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
03821050	DECO 10W E14 240-250V T17 CL 1CT/10X10F	-	240-250 V	10.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
25008750	Deco 7.0W E14 230-240V T17 CL 1CT/10X10F	7 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
03821050	DECO 10W E14 240-250V T17 CL 1CT/10X10F	10 kWh

