



Product Description

Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

Versions



LPPR_ITUBAPE_E14_T22_CL-
Product photo



LPPR_ITUBAPE_E14_T25_CL-
Product photo

Appliance Oven Tubular

Versions






15 W E14 cap Incandescent
appliance bulb - RFT



15 W E14 cap Oven Incandescent
appliance bulb - RFT

Dimensional drawing



Product	D (max)	C (max)
15 W E14 cap Oven Incandescent appliance bulb	22 mm	49 mm
15 W E14 cap Oven Incandescent appliance bulb	22 mm	49 mm
App 15.4W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

Product	D (max)	C (max)
App 26.0W E14 230-240V T25 CL OV 1CT	25 mm	57 mm
App 26.0W E14 230-240V T25CL OV 1CT/20F	25 mm	57 mm

Product	D (max)	C (max)
10 W E14 cap Clear Incandescent tubular bulb	26 mm	59 mm

Appliance Oven Tubular

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Switching Cycle	4,000
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230-240 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Light Technical

Order Code	Full Product Name	Luminous Flux
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	90 lm
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	172 lm
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	172 lm
924198344441	10 W E14 cap Clear Incandescent tubular bulb	34 lm
924196244451	15 W E14 cap Oven Incandescent appliance bulb	90 lm
924196244452	15 W E14 cap Oven Incandescent appliance bulb	90 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	0.06 A	15.0 W
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	0.11 A	25.0 W
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	0.11 A	25.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
924198344441	10 W E14 cap Clear Incandescent tubular bulb	0.04 A	10.0 W
924196244451	15 W E14 cap Oven Incandescent appliance bulb	0.06 A	15.0 W
924196244452	15 W E14 cap Oven Incandescent appliance bulb	0.06 A	15.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	T22
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	T25
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	T25

Order Code	Full Product Name	Bulb Shape
924198344441	10 W E14 cap Clear Incandescent tubular bulb	T25
924196244451	15 W E14 cap Oven Incandescent appliance bulb	T22
924196244452	15 W E14 cap Oven Incandescent appliance bulb	T22

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	15 kWh
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	25 kWh
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	25 kWh
924198344441	10 W E14 cap Clear Incandescent tubular bulb	10 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
924196244451	15 W E14 cap Oven Incandescent appliance bulb	15 kWh
924196244452	15 W E14 cap Oven Incandescent appliance bulb	15 kWh

Appliance Oven Tubular

