



# Brighten your home with infinite possibilities

## DuraMax Deco Blunt Tip

Philips DuraMax® Long Life Decorative blunt tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative blunt tip bulbs are available in a variety of shapes, sizes and wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

### Benefits

- Philips DuraMax long life decorative blunt tip light bulbs last longer than standard incandescent, significantly reducing the hassle of replacing light bulbs that burn out too quickly.
- Philips DuraMax decorative blunt tip bulbs add a pleasant touch to home décor.

### Features

- Lasts at Least OneYear!\*
- Available in a variety of wattages.
- Frosted light bulbs provide soft white light.
- Clear light bulbs provide decorative sparkle.
- Candelabra and medium base.
- Available in BA9.5 shape with medium base: 25 watt clear and 40, and 60 watts clear and frost; B10.5 shape with candleabra base: 25, 40, and 60 watts; B13 shape with medium base: 25, 40, and 60 watt clear.
- \*Based on an average of hours usage per day/7 days per week. Hours differ between products, and there are exceptions. See individual products for details.

# DuraMax Deco Blunt Tip

## Application



- Ideal for general or ambient lighting in wall sconces, chandeliers, and other decorative light fixtures.

## Versions



LPPR I-B B13 CL

## Dimensional drawing



Product
BC25B10-1/2C/CL/LL 120V 6/2TP
BC40B10-1/2C/CL/LL 120V 6/2TP
BC60B10-1/2C/CL/LL 120V 6/2TP

Product
BC40B13/CL/LL 120V 6/2 TP
BC40ETC/D/LL 6/2PK

# DuraMax Deco Blunt Tip

General Information	
Rated Lifetime (Hours)	2,000 hour(s)
Operating Position	S90
Operating and Electrical	
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

## General Information

Order Code	Full Product Name	Cap-Base
925169736301	BC40ETC/D/LL 6/2PK	E26
925247836306	BC40B13/CL/LL 120V 6/2 TP	E26
925288336308	BC25B10-1/2C/CL/LL 120V 6/2TP	E12

Order Code	Full Product Name	Cap-Base
925288536307	BC40B10-1/2C/CL/LL 120V 6/2TP	E12
925288736309	BC60B10-1/2C/CL/LL 120V 6/2TP	E12

## Light Technical

Order Code	Full Product Name	Luminous Flux
925169736301	BC40ETC/D/LL 6/2PK	266 lm
925247836306	BC40B13/CL/LL 120V 6/2 TP	300 lm
925288336308	BC25B10-1/2C/CL/LL 120V 6/2TP	150 lm

Order Code	Full Product Name	Luminous Flux
925288536307	BC40B10-1/2C/CL/LL 120V 6/2TP	300 lm
925288736309	BC60B10-1/2C/CL/LL 120V 6/2TP	550 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
925169736301	BC40ETC/D/LL 6/2PK	40 W
925247836306	BC40B13/CL/LL 120V 6/2 TP	40 W
925288336308	BC25B10-1/2C/CL/LL 120V 6/2TP	25 W

Order Code	Full Product Name	Power Consumption
925288536307	BC40B10-1/2C/CL/LL 120V 6/2TP	40 W
925288736309	BC60B10-1/2C/CL/LL 120V 6/2TP	60 W

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
925169736301	BC40ETC/D/LL 6/2PK	B13
925247836306	BC40B13/CL/LL 120V 6/2 TP	B13
925288336308	BC25B10-1/2C/CL/LL 120V 6/2TP	B10 1/2

Order Code	Full Product Name	Bulb Shape
925288536307	BC40B10-1/2C/CL/LL 120V 6/2TP	B10 1/2
925288736309	BC60B10-1/2C/CL/LL 120V 6/2TP	B10 1/2

