



# Sign

## Sign

Philips Sign bulbs provide the perfect light for dramatic accents and display lighting that is great for hard to reach signs, indoors and out.

### Benefits

- Great for hard to reach signs.

### Features

- Long life bulb.
- Available in S14: Clear and Frost:10 watt and S14: Clear,Frost and White: 11 watt.

### Application

- Ideal for indoor and outdoor signs.

## Versions





LPPR I-T E17 ALC T6-12 FR



LPPR I-T E17 T7 CL

Dimensional drawing



General Information	
Operating Position	UNIVERSAL
Operating and Electrical	
Voltage (Nom)	120 V

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
920603636301	20T6-1/2/IF 120V 24PK	E17	1,000 hour(s)

Light Technical

Order Code	Full Product Name	Luminous Flux
920603636301	20T6-1/2/IF 120V 24PK	150 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
920603636301	20T6-1/2/IF 120V 24PK	20 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
920603636301	20T6-1/2/IF 120V 24PK	Frosted	T-6 1/2

Product
BC-25T10/CL

Product
20T6-1/2/IF 120V 24PK

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
925195136301	BC-25T10/CL	E26	1,500 hour(s)

Order Code	Full Product Name	Luminous Flux
925195136301	BC-25T10/CL	200 lm

Order Code	Full Product Name	Power Consumption
925195136301	BC-25T10/CL	25 W

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925195136301	BC-25T10/CL	Clear	T-10

Sign

